

UM 45-SES - Lateral element

2959308

<https://www.phoenixcontact.com/us/products/2959308>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element, with marker groove, labeling with SS-ZB. Width: 11 mm, length: 45 mm, height: 21 mm

Your advantages

- Easy installation
- Flexible size and shape
- Inexpensive as a result of reducing the number of separate housing parts

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2959308 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | AC13 |
| Product key | ACHDBA |
| GTIN | 4017918117597 |
| Weight per piece (including packing) | 3.84 g |
| Weight per piece (excluding packing) | 3.68 g |
| Customs tariff number | 39269097 |
| Country of origin | PL |

UM 45-SES - Lateral element

2959308

<https://www.phoenixcontact.com/us/products/2959308>




Technical data

Product properties

| | |
|----------------|-------------------------------|
| Product type | Panel mounting base side part |
| Housing type | Press-drawn section housings |
| Housing series | UM |
| Product family | UM SE |
| Type | Lateral element |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 11 mm |
| Height | 45 mm |
| Depth | 21 mm |

Material specifications

| | |
|--|------------------|
| Color (Housing) | green (RAL 6021) |
| Flammability rating according to UL 94 | V0 |
| Housing material | PA |
| Surface characteristics | untreated |

Environmental and real-life conditions

| | |
|---------------------------------|--|
| Ambient conditions | |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |

UM 45-SES - Lateral element


2959308

<https://www.phoenixcontact.com/us/products/2959308>



Drawings

Dimensional drawing



UM 45-SES - Lateral element

2959308

<https://www.phoenixcontact.com/us/products/2959308>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2959308>



UL Recognized

Approval ID: E240868

UM 45-SES - Lateral element



2959308

<https://www.phoenixcontact.com/us/products/2959308>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM 45-SES - Lateral element

2959308

<https://www.phoenixcontact.com/us/products/2959308>



Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com