**Part Number :** 1300250543
**Product Description :** Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), DeviceNet Standard Cable, 1.0m (3.28') Length
**Series Number :** 130025
**Status :** Not Recommended For New Design
**Product Category :** Industrial Cable Assemblies
**Engineering Part Number :** DND99A-M010



## Documents and Resources

### Drawings

1300250543_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Not Recommended For New Design |
| Category | Industrial Cable Assemblies |
| Series | 130025 |
| Description | Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), DeviceNet Standard Cable, 1.0m (3.28') Length |
| Comments | A-Size (7/8" - 16 UN-2A) |
| IP Rating | IP67 |
| Product Name | DeviceNet Trunk,Mini-Change |
| Type | Double Ended |
| UPC | 78172504387 |

### Agency

| | |
|---|---|
| CSA | LR6837 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum | 300V AC/DC |

### Physical

| | |
|---|---|
| Cable Diameter | 7.24mm (.285") |
| Cable Length | 1.0m (3.28') |
| Color - Cable Jacket | Gray |
| Connector End A | Mini-Change |
| Connector End B | Mini-Change |
| Coupling Style | Threaded |
| Gender | Female-Male |
| Keyway | Single |
| LED Indicator | None |

Downloaded from Arrow.com.

| | |
|---|---|
| Material - Cable Jacket | PVC |
| Material - Connector Body | PVC |
| Material - Contact | Brass |
| Material - Coupling Nut | Zinc Die-Cast |
| Material - Plating Mating | Gold |
| Orientation | 90° to 90° |
| Poles | 5 |
| Temperature Range - Operating | -20° to +80°C |
| Wire/Cable Type | Thin Standard Cable |
| Wire Size (AWG) | 22 |



Downloaded from Arrow.com.