





Copyright FCI.





PRODUCT NO
10046971-023LF




- NOTE:
1. MATERIAL:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
UL 94 V-0 FLAME RETARDANT.
TERMINAL: HIGH CONDUCTIVITY COPPER ALLOY.
PLATING SPEC AS BELOW:
Ni 50u" UNDER PLATED.
Au 30u" OVER CONTACT AREA.(ONE SIDE)
MATTE TIN 120u" OVER SOLDERING AREA.
2. PACKING SPEC. GS-14-937
3. PRODUCT SPEC. GS-12-338.
4. MANUFACTURER'S NAME, P/N AND DATE CODE
TO APPEAR ON THIS SURFACE AS PER GS-24-007.
5. PART NUMBER 10046971-023LF MEETS EUROPEAN UNION DIRECTIVE AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS
IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.


rev	ecn no	dr	date
A	DG10-0289	SM	08/23/10
B	DG10-0456	WL	12/28/10
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface 		tolerance std		projection 			
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JULIA WANG	2009-03-19	ANGULAR	LINEAR	0.X	±0.5	size	A4	Scale	1.000
Eng	JULIA WANG	2009-03-19			0.XX	±0.25				
Chr	PM ZHENG	2009-03-19			0°. ±2°	0.XXX				
Appr	JOSEPH HSIA	2009-03-19	Product family					ECN DG10-0456		
								Spec ref *		
		title	POWER EDGE CONNECTOR				dwg no	10046971-023		Rev
			VERTICAL TYPE (25PX2)							
			catalog no							
			* CUSTOMER COP							
								sheet 1 of 2		B





AND THE THICKNESS IS 1.57mm



DETAIL A
SCALE 5.000