


PRODUCT DATA DRAWING

REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
-	NRN 42265	05/18	STW
A	DCN 47843	8/18	STW



MATERIAL:

CONNECTORS: SMA MALE (SF2915-6001), SMPM FEMALE (3222-40002)


CABLE: T-FLEX 405

SHRINK TUBING: M23053/5

PERFORMANCE:

IMPEDANCE: 50 OHMS
FREQ. RANGE: DC TO 12.4 GHz
VSWR: 1.60:1 MAX, DC TO 12.4 GHz
INSER. LOSS: SEE TABLE

TABLE 1		
SV P/N	OAL	MAX INSER. LOSS
7032-7240	6.000	0.85 dB
7032-7241	12.000	1.27 dB
7032-7242	24.000	2.12 dB

MATERIAL: SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: $\pm 1/64$ ANGULAR: X° $\pm 1^{\circ}0'$ X°X' $\pm 15'$ DECIMAL: .X $\pm .030$.XX $\pm .010$.XXX $\pm .005$ INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		 www.svmicrowave.com TITLE: SMPM R/A FEMALE TO SMA R/A MALE FOR T-FLEX 405	
FINISH: SEE NOTES					
SURFACE AREA: N/A	THIRD ANGLE PROJECTION		DRAWN: DEF 05/07/18	SIZE DWG. NO. 7032-7240-7242	
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.			CHECKED: STW 05/07/18		
			APPROVED: STW 05/07/18	SCALE: 1:2	SHEET 1 OF 1