


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - in.					TOOLS
		A ± .03	W ± .01	C ± .02	M ± .03	H ± .01	
PV14-6LF	#6	.90 (22.86)	.25 (6.35)	.22 (5.59)	.68 (17.27)	.14 (3.56)	*CT-100A **CT-600-A (CT-500CH) **CT-600-A (CT-550CH) **CT-1550 **CT-1551 **CT-2500 (CT-2550CH)
PV14-6LFW	#6	.90 (22.86)	.29 (7.37)	.22 (5.59)	.68 (17.27)	.14 (3.56)	
PV14-8LF	#8	.97 (24.64)	.29 (7.37)	.25 (6.35)	.73 (18.54)	.16 (4.06)	
PV14-10LF	#10	.97 (24.64)	.33 (8.38)	.25 (6.35)	.73 (18.54)	.19 (4.83)	
PV14-10LFN	#10	.97 (24.64)	.29 (7.37)	.25 (6.35)	.73 (18.54)	.19 (4.83)	

NOTES:

*USED FOR #16-14 AWG SOLID OR STRANDED COPPER WIRE
& 167° F (75° C) MAX TEMP. RATING
 **USED FOR #18-14 AWG SOLID OR STRANDED COPPER WIRE
& 221° F (105° C) MAX TEMP. RATING

1. cULus LISTED FOR:
A. 600V MAX. BLDG WIRE
(1000 V MAX. IN SIGNS, FIXTURES & LUMINARIES)
2. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
3. MATERIAL:
A. STAMPING - .032" THK, COPPER
TIN PLATED
B. HOUSING - VINYL, BLUE
C. SLEEVE - BRASS, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. WIRE STRIP LENGTH: $5/16 + 1/32$ (7.9 + .8)
- 0 - 0



TITLE
**#16-14 BARREL FUNNELED VINYL INSULATED LOCKING
 FORK, .175 [4.45] MAX. WIRE INSULATION DIAMETER**

CUSTOMER DRAWING

ITEM REVISION NAME

N41296BB/10


DATASET FILE NAME

N41296BB/10

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ±
 .XX ±

.XXX ±
 ANGLES ±



THIRD ANGLE
 PROJECTION

MATERIAL:

SEE NOTES

DRAWING NUMBER:

A41296

10	07/14	MBY	JHNU	RGB	REVISED NOTES, MOVED TOOLS TO TABLE, REVISED CERTIFICATION, UPDATED BORDER	N41296BB-A41296			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN			

DRAWN BY	DATE	CHK	SCALE		SIZE
DAW		CJH	NONE	SHT 1 OF 1	A