IGBT - Field Stop, Trench
650 V, 50 A
FGH50T65SQD

V_{CES}	I_C
650 V	50 A





TO−247−3LD
CASE 340CH

Description

Using novel field stop IGBT technology, **onsemi**'s new series of field stop 4th generation IGBTs offer the optimum performance for solar inverter, UPS, welder, telecom, ESS and PFC applications where low conduction and switching losses are essential.

Features

- Max Junction Temperature T_J = 175°C
- Positive Temperature Co−efficient for Easy Parallel Operating
- High Current Capability
- Low Saturation Voltage: $V_{CE(sat)}$ = 1.6 V (Typ.) @ I_C = 50 A
- 100% of the Parts Tested for I_{LM}
- High Input Impedance
- Fast Switching
- Tighten Parameter Distribution
- This Device is Pb−Free and is RoHS Compliant

Applications

- Solar Inverter, UPS, Welder, Telecom, ESS, PFC

MARKING DIAGRAM



$Y	= **onsemi** Logo
&Z	= Assembly Plant Code
&3	= Numeric Date Code
&K	= Lot Code
FGH50T65SQD	= Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 2 of this data sheet.

© Semiconductor Components Industries, LLC, 2016

Downloaded from Arrow.com.

ABSOLUTE MAXIMUM RATINGS

Symbol	Description		FGH50T65SQD−F155	Unit
V_{CES}	Collector to Emitter Voltage		650	V
V_{GES}	Gate to Emitter Voltage		±20	V
	Transient Gate to Emitter Voltage		±30	V
I_C	Collector Current	T_C = 25°C	100	A
		T_C = 100°C	50	A
I_{LM} (Note 1)	Pulsed Collector Current	T_C = 25°C	200	A
I_{CM} (Note 2)	Pulsed Collector Current		200	A
I_F	Diode Forward Current	T_C = 25°C	50	A
	Diode Forward Current	T_C = 100°C	30	A
I_{FM}	Pulsed Diode Maximum Forward Current		200	A
P_D	Maximum Power Dissipation	T_C = 25°C	268	W
		T_C = 100°C	134	W
T_J	Operating Junction Temperature		−55 to +175	°C
T_{STG}	Storage Temperature Range		−55 to +175	°C
T_L	Maximum Lead Temp. for Soldering Purposes, 1/8” from Case for 5 Seconds		300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. V_{CC} = 400 V, V_{GE} = 15 V, I_C = 200 A, R_G = 3 Ω, Inductive Load.
2. Repetitive rating: Pulse width limited by max. junction temperature.

THERMAL CHARACTERISTICS

Symbol	Parameter	FGH50T65SQD−F155	Unit
$R_{\theta JC}$ (IGBT)	Thermal Resistance, Junction to Case, Max.	0.56	°C/W
$R_{\theta JC}$ (Diode)	Thermal Resistance, Junction to Case, Max.	1.25	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max.	40	°C/W

PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Qty per Tube
FGH50T65SQD−F155	FGH50T65SQD	TO−247−3LD	Tube	−	−	30

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS OF THE IGBT (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
BV_{CES}	Collector to Emitter Breakdown Voltage	V_{GE} = 0 V, I_C = 1 mA	650	–	–	V
$\Delta BV_{CES} / \Delta T_J$	Temperature Coefficient of Breakdown Voltage	I_C = 1 mA, Reference to 25°C	–	0.6	–	V/°C
I_{CES}	Collector Cut−Off Current	V_{CE} = V_{CES}, V_{GE} = 0 V	–	–	250	μA
I_{GES}	G−E Leakage Current	V_{GE} = V_{GES}, V_{CE} = 0 V	–	–	±400	nA
ON CHARACTERISTICS						
$V_{GE(th)}$	G−E Threshold Voltage	I_C = 50 mA, V_{CE} = V_{GE}	2.6	4.5	6.4	V
$V_{CE(sat)}$	Collector to Emitter Saturation Voltage	I_C = 50 A, V_{GE} = 15 V, T_C = 25 °C	–	1.6	2.1	V
		I_C = 50 A, V_{GE} = 15 V, T_C = 175°C	–	1.92	–	V
DYNAMIC CHARACTERISTICS						
C_{ies}	Input Capacitance	V_{CE} = 30 V, V_{GE} = 0 V, f = 1MHz	–	3275	–	pF
C_{oes}	Output Capacitance		–	84	–	pF
C_{res}	Reverse Transfer Capacitance		–	12	–	pF
SWITCHING CHARACTERISTICS						
$T_{d(on)}$	Turn−On Delay Time	V_{CC} = 400 V, I_C = 12.5 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, T_C = 25°C	–	22	–	ns
T_r	Rise Time		–	8.7	–	ns
$T_{d(off)}$	Turn−Off Delay Time		–	105	–	ns
T_f	Fall Time		–	2.5	–	ns
E_{on}	Turn−On Switching Loss		–	180	–	μJ
E_{off}	Turn−Off Switching Loss		–	45	–	μJ
E_{ts}	Total Switching Loss		–	225	–	μJ
$T_{d(on)}$	Turn−On Delay Time	V_{CC} = 400 V, I_C = 25 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, T_C = 25°C	–	19	–	ns
T_r	Rise Time		–	13	–	ns
$T_{d(off)}$	Turn−Off Delay Time		–	93	–	ns
T_f	Fall Time		–	6.4	–	ns
E_{on}	Turn−On Switching Loss		–	410	–	μJ
E_{off}	Turn−Off Switching Loss		–	88	–	μJ
E_{ts}	Total Switching Loss		–	498	–	μJ
$T_{d(on)}$	Turn−On Delay Time	V_{CC} = 400 V, I_C = 12.5 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, T_C = 175°C	–	20	–	ns
T_r	Rise Time		–	9.8	–	ns
$T_{d(off)}$	Turn−Off Delay Time		–	116	–	ns
T_f	Fall Time		–	3.5	–	ns
E_{on}	Turn−On Switching Loss		–	402	–	μJ
E_{off}	Turn−Off Switching Loss		–	110	–	μJ
E_{ts}	Total Switching Loss		–	512	–	μJ

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS OF THE IGBT (T_C = 25°C unless otherwise noted) (continued)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS						
$T_{d(on)}$	Turn−On Delay Time	V_{CC} = 400 V, I_C = 25 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, T_C = 175°C	–	18	–	ns
T_r	Rise Time		–	15	–	ns
$T_{d(off)}$	Turn−Off Delay Time		–	102	–	ns
T_f	Fall Time		–	8	–	ns
E_{on}	Turn−On Switching Loss		–	641	–	μJ
E_{off}	Turn−Off Switching Loss		–	203	–	μJ
E_{ts}	Total Switching Loss		–	844	–	μJ
Q_g	Total Gate Charge	V_{CE} = 400 V, I_C = 50 A, V_{GE} = 15 V	–	99	–	nC
Q_{ge}	Gate to Emitter Charge		–	17	–	nC
Q_{gc}	Gate to Collector Charge		–	23	–	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

ELECTRICAL CHARACTERISTICS OF THE DIODE (T_C = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions		Min	Typ	Max	Unit
V_{FM}	Diode Forward Voltage	I_F = 30 A	T_C = 25°C	–	2.2	2.6	V
			T_C = 175°C	–	1.9	–	
E_{rec}	Reverse Recovery Energy	I_F = 30 A, dI_F/dt = 200 A/μs	T_C = 175°C	–	40	–	μJ
T_{rr}	Diode Reverse Recovery Time		T_C = 25°C	–	31	–	ns
			T_C = 175°C	–	207	–	
Q_{rr}	Diode Reverse Recovery Charge		T_C = 25°C	–	48	–	nC
			T_C = 175°C	–	820	–	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS



Figure 1. Typical Output Characteristics



Figure 2. Typical Output Characteristics



Figure 3. Typical Saturation Voltage Characteristics



Figure 4. Saturation Voltage vs. Case Temperature at Variant Current Level



Figure 5. Saturation Voltage vs. V_{GE}



Figure 6. Saturation Voltage vs. V_{GE}

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (Continued)



Figure 7. Capacitance Characteristics



Figure 8. Gate Charge Characteristics



Figure 9. Turn−on Characteristics vs. Gate Resistance



Figure 10. Turn−off Characteristics vs. Gate Resistance



Figure 11. Switching Loss vs. Gate Resistance



Figure 12. Turn−on Characteristics vs. Collector Current

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (Continued)



Figure 13. Turn−off Characteristics vs. Collector Current



Figure 14. Switching Loss vs. Collector Current



Figure 15. Load Current vs. Frequency



Figure 16. SOA Characteristics



Figure 17. Forward Characteristics



Figure 18. Reverse Recovery Current

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (Continued)



Figure 19. Reverse Recovery Time



Figure 20. Stored Charge



Figure 21. Transient Thermal Impedance of IGBT



Figure 22. Transient Thermal Impedance of Diode

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TO−247−3LD
CASE 340CH
ISSUE A

DATE 09 OCT 2019



NOTES: UNLESS OTHERWISE SPECIFIED.

A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
B. ALL DIMENSIONS ARE IN MILLIMETERS.
C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.58	4.70	4.82
A1	2.29	2.475	2.66
A2	1.40	1.50	1.60
D	20.32	20.57	20.82
E	15.37	15.62	15.87
E2	4.96	5.08	5.20
e	~	5.56	~
L	19.75	20.00	20.25
L1	3.69	3.81	3.93
ØP	3.51	3.58	3.65
Q	5.34	5.46	5.58
S	5.34	5.46	5.58
b	1.17	1.26	1.35
b2	1.53	1.65	1.77
b4	2.42	2.54	2.66
c	0.51	0.61	0.71
D1	13.08	~	~
D2	0.51	0.93	1.35
E1	12.81	~	~
ØP1	6.61	6.73	6.85

GENERIC
MARKING DIAGRAM*



XXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON13853G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**TO−247−3LD**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.