



## Product Navigation

[Home](#) [About Us](#) [Products](#) [Investor Relations](#) [News](#) [Contact Us](#) [Secure EAX](#)

### Circuit Board Indicators

### Panel Mount Indicators

### Solid State Lighting

### Traffic Signals

### Vehicle Lighting

### Rail

### Obstruction Lighting

### Hazardous Area Lighting

### Heliport Lighting

#### how to purchase

 [sales contacts](#)

 [stock check](#)

#### search

 [Product Line Search](#)

Please select a Product Line to search.

[Circuit Board Indicators](#) 

 [find](#)

 [Part # / Text Search](#)

**Part No.:**

**Text Search:**

 [search](#)

#### quick links

##### Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

##### Application Notes FAQs

**Dialight Ltd (UK)**  
**Dialight Garufo**  
**Dialight BLP**  
**LumiDrives**

| Circuit Board Indicators - Through Hole Indicators |  |
|--|--|
| P/N# 5680714444F                                   | 3 mm Lens  |
| Description  | 3 mm Backlighting Quad-Level CBI Y/G-Y/G-Y/G-Y/G |
| Package Options                                    | 5 Pieces Per Bag                                 |
| Product Type                                       | Through Hole Indicators                          |
| Sub Product Type                                   | with Quad Level Housing                          |
| Configuration                                      | 3 mm Lens  |
| Viewing  | Right Angle                                      |
| Viewing Angle                                      | 80   |
| Test Current (mA)                                  | 10mA   |

#### Absolute Maximum Ratings (Ta = 25°)

|                |                |
|----------------|----------------|
| Solder Temp    | 260° for 5 sec |
| Operating Temp | -55 to +100° C |
| Storage Temp   | -55 to +100° C |



view PDF

#### Operating Characteristics

|                            |                           |
|----------------------------|---------------------------|
| LED Position               | Found in position(s): 1-4 |
| Color                      | Yellow / Green            |
| Lamp Type                  | Bi-Color / Bi-Color       |
| LED Type                   |                           |
| Intensity Min (mcd)        | 2.5 / 2.5                 |
| Intensity Typ (mcd)        | 4.3 / 6.3                 |
| Intensity Max (mcd)        |                           |
| Fwd Voltage Min            |                           |
| Fwd Voltage Typ            |                           |
| Fwd Voltage Max            |                           |
| Dom Wavelength Min (nm)    | 587 / 569                 |
| Dom Wavelength Typ (nm)    |                           |
| Dom Wavelength Max (nm)    |                           |
| Power Dissipation Max (mW) | 60 / 100                  |
| Backlighting               |                           |
| Pitch Between Vertical     |                           |
| Pitch Between Horizontal   |                           |
| Lum Intensity Min          |                           |
| Lum Intensity Typ          |                           |
| Lum Intensity Max          |                           |

#### Distributor Stock Check

Check stock with our distributors now.

5680714444F

 [check stock](#)