




**Part Number :** [151350603](#)

**Product Description :** CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 300.00mm Length, 6 Circuits, Beige

**Series Number :** 15135

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies



---

## Documents and Resources


### Drawings

[151350603\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant  |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21  |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)  |
| EU RoHS            | Compliant per EU 2015/863   |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|                        |   |
|------------------------|---|
| Status                 | Active  |
| Category               | Power and Signal Cable Assemblies   |
| Series                 | 15135   |
| Description            | CLIK-Mate-to-CLIK-Mate Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 300.00mm Length, 6 Circuits, Beige |
| Application            | Signal, Wire-to-Board   |
| Assembly Configuration | Dual Ended Connectors   |
| Connector to Connector | CLIK-Mate-to-CLIK-Mate  |
| Product Name           | CLIK-Mate   |
| Type                   | Discrete Wire Assembly  |
| UPC                    | 191128160339  |

#### Electrical

|                               |                  |
|-------------------------------|------------------|
| Current - Maximum per Contact | 2.0A             |
| Voltage - Maximum             | 100V AC (RMS)/DC |

#### Physical

|                           |              |
|---------------------------|--------------|
| Cable Length              | 300.00mm     |
| Circuits (Loaded)         | 6            |
| Circuits (maximum)        | 6            |
| Color - Resin             | Beige        |
| Gender                    | Male-Male    |
| Lock to Mating Part       | Yes          |
| Material - Metal          | Copper Alloy |
| Material - Plating Mating | Tin          |

|                                |                                  |
|--------------------------------|----------------------------------|
| Material - Plating Termination | Tin                              |
| Material - Resin               | Polybutylene Terephthalate (PBT) |
| Net Weight                     | 6.544/g                          |
| Number of Rows                 | 1                                |
| Overmolded                     | No                               |
| Packaging Type                 | Bag                              |
| Pitch - Mating Interface       | 1.50mm                           |
| Plating min - Mating           | 0.406µm                          |
| Plating min - Termination      | 0.406µm                          |
| Single Ended                   | No                               |
| Termination Interface Style    | Crimp or Compression             |
| Wire/Cable Type                | UL 1061                          |
| Wire Size (AWG)                | 24                               |

---

## Mates With / Use With

### Mates with Part(s)

| Description  | Part Number                   |
|--|-------------------------------|
| 1.50mm Pitch CLIK-Mate Bottom Entry Single Row PCB Receptacles | <a href="#"><u>503395</u></a> |
| 1.50mm Pitch CLIK-Mate Right-Angle Single Row PCB Receptacles  | <a href="#"><u>503175</u></a> |
| 1.50mm Pitch CLIK-Mate Right-Angle Single Row PCB Receptacles  | <a href="#"><u>502585</u></a> |
| 1.50mm Pitch CLIK-Mate Vertical Single Row PCB Receptacles     | <a href="#"><u>503159</u></a> |
| 1.50mm Pitch CLIK-Mate Vertical Single Row PCB Receptacles     | <a href="#"><u>502584</u></a> |

---

This document was generated on May 04, 2026