

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2012
© COPYRIGHT 2009 BY TE CONNECTIVITY ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED (ECR-25-262025)	12NOV2025	SW	YH
	D1	REVISED (ECR-23-171026)	31MAR2023	CI	KT





ISOMETRIC VIEW







SECTION A-A









<TABLE 1>

TYPE	FINISH	P/N	WIRE RANGE(mm²)	
.025	PRE-TIN	2005098-1	0.22	
		2005154-1	0.37~0.56	
	GOLD	2005154-2	0.3~0.5	D
.090	PRE-TIN	1897752-1	0.22~0.56	
		368088-1	0.3~0.5	
		368087-1	0.85~1.25	
		368086-1	2.0~2.5	
	GOLD	1-368088-1	0.3~0.5	D

NOTE
1. GENERAL TOLERANCE: ±0.3, ±3°
2. CONDITION OF DELEVERY
   DBL IN 1st LOCKING POSITION
3. APPLICABLE PLUG ASS'Y P/N: x-200543 1-x
4. APPLICABLE TAB CONTACT P/N: <TABLE 1>

2005434-6	2005434-4	2005434-1	ASS'Y P/N
HYB 34P CAP ASS'Y	HYB 34P CAP ASS'Y	HYB 34P CAP ASS'Y	DESCRIPTION

NO	FINISH/COLOR	MATERIAL	DESCRIPTION	Q'TY		
2	WHITE	PBT	CAP DBL HSG	1	1	1
1	RED	PBT	CAP HSG	1		
	BROWN	PBT	CAP HSG		1	
	WHITE	PBT	CAP HSG			1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL SEE TABLE

FINISH

DWN CH PARK
CHK JW JUNG
APVD HG CHO
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

TE Connectivity

NAME 025/090 HYBRID 34P CAP ASS'Y

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2005434	

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV D2

Downloaded from Arrow.com.