Document No. : SXC12754-00

KYOCERA SAW Filter

– WiFi-2.4GHz Filter –

Type Name : VF14-2442M5UUB1

Mar., 31, 2025

KYOCERA Corporation

Corporate Electronic Components Group


Electronic Devices Division

© 2025 KYOCERA Corporation all right reserved


Downloaded from Arrow.com.

Dimensions & Test Circuit of SAW Filter

Dimensions



Test Circuit (TBD)



L1 : 3.6nH (Ideal)
L2 : 3.9nH (Ideal)

Each port
Port extension(Time) : 100ps
Port extension(Loss) : 0.206dB

Unit	:	mm
V	:	Identification mark
W4	:	Identification no.
●	:	Index mark of pin 1
XXXX	:	Production code

Pin allocation

Pin No.	Function
(1)	Input
(2)	GND
(3)	GND
(4)	Output
(5)	GND

© 2025 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.

Rating

Items		Rating	Unit	Note
Operating Temperature Range		-40 to 105	deg.C	
Storage Temperature Range		-40 to 105	deg.C	
Max Input Power In Band		25	dBm	5,000Hours,Ta=50deg.C ,CW
ESDLevel	Human Body Model	100	Volt	Complied to JESD22-A114
Moisture Sensitivity Level		3		Complied to J-STD-033B.1
Input Port Nominal Impedance		50 // 3.6nH (shunt)	ohm	Unbalance
Output Port Nominal Impedance		50 // 3.9nH (shunt)	ohm	Unbalance
AEC-Q200		Grade 2		Complied to AEC-Q200

© 2025 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.


Characteristic table


Items	Frequency (MHz)			Unit	Kyocera Specification			Note
					min.	typ.	max.	
Insertion Loss	2400	to	2483.5	dB	-	1.5	2.6	
Ripple	2400	to	2483.5	dB	-	0.5	2.0	
Input VSWR	2400	to	2483.5	-	-	1.5	2.2	
Output VSWR	2400	to	2483.5	-	-	1.5	2.2	
Attenuation	50	to	1000	dB	40	58	-	
	1000	to	2100	dB	38	42	-	
	2100	to	2320	dB	38	42	-	
	2320	to	2332.5	dB	40	59	-	
	2332.5	to	2345	dB	38	50	-	
	2600	to	3100	dB	30	42	-	
	3100	to	4000	dB	30	42	-	
	4000	to	5000	dB	40	48	-	

© 2025 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.


Curve Data






VF14-2442M5UUB1

Specification





© 2025 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.

Notice

1. Characteristics described in this datasheet are for references specifications shall be based on written documents agreed by each party.

2. Contents in this datasheet are subject to change without notice. It is recommended to confirm the latest information at the time of usage. Also, this datasheet is revised once a year. We may not be able to accept requests based on old datasheets.

3. Products in this datasheet are intended to be used in general electronic equipment such as office equipment, audio and visual equipment, communication equipment, measurement instrument and home appliances. It is absolutely recommended to consult with our sales representatives in advance upon planning to use our products in applications which require extremely high quality and reliability such as aircraft and aerospace equipment, traffic systems, safety systems, power plant and medical equipment including life maintenance systems.

4. Even though we strive for improvements of quality and reliability of products, it is requested to design with enough safety margin in equipment or systems in order not to threaten human lives directly or damage human bodies or properties by an accidental result of products.

5. It is requested to design based on guaranteed specifications for such as maximum ratings, operating voltage and operating temperature. It is not the scope of our guarantee for unsatisfactory results due to misuse or inadequate usage of products in the datasheet.

6. Operation summaries and circuit examples in this datasheet are intended to explain typical operation and usage of the product. It is recommended to perform circuit and assembly design considering surrounding conditions upon using products in this datasheet.

7. Technical information described in this datasheet is meant to explain typical operations and applications of products, and it is not intended to guarantee or license intellectual properties or other industrial rights of the third party or Kyocera.

8. Trademarks, logos and brand names used in this datasheet are owned by Kyocera or the corresponding third party.

9. Certain products in this datasheet are subject to the Foreign Exchange and Foreign Trade Control Act of Japan, and require the license from Japanese Government upon exporting the restricted products and technical information under the law. Besides, it is requested not to use products and technical information in the datasheet for the development and/or manufacture of weapons of mass destruction or other conventional weapons, nor to provide them to any third party with the possibility of having such purposes.

10. It is prohibited to reprint and reproduce a part or whole of this datasheet without permission.

© 2025 KYOCERA Corporation all right reserved

Downloaded from Arrow.com.