


- NOTES:
- 1. MATERIALS AND FINISHES
 - BODY – BRASS, NICKEL PLATING
 - CONTACT – BERYLLIUM COPPER, SILVER PLATING
 - INSULATOR – PTFE, NATURAL
 - 2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM
 - B. FREQUENCY RANGE: DC 0–11 GHz
 - C. DIELECTRIC WITHSTANDING VOLTAGE: 2500 VRMS, MIN.
 - 3. MECHANICAL:
 - A. DURABILITY: 500 CYCLES MIN.
 - B. TEMPERATURE RANGE: – 65°C to +165°C

THIRD ANGLE PROJ.



REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
Y	REDRAWN TO UPDATE FORMAT	5-Jan-09'	47205	SH
AA	STAMP "AMPHENOL" WAS "74868"\RD-DM11120601R3		48845	



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 – 6mm 6 – 30mm 30 – 120mm ANGLES ±0.1mm ±0.2mm ± 0.3mm ±1°</p> <p>NOTICE – These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.</p>	MATERIAL	DRAWN R.MAO	DATE 12-Dec-11	TITLE N ADAPTER JACK TO JACK UG-29A/U			Amphenol RF	
	REFERENCE	ENGINEER N.CAO	DATE 07-May-03				Danbury CT USA, Tainan Taiwan, Shenzhen China www.amphenolrf.com	
		APPROVED S.HSIEH	DATE 12-Dec-11	SCALE: 2.5/1	SHEET	2 OF 2	DRAWING NO.	82-65
	FINISH	F:\DWG\CNPD\82\65-AASZ		DWG SIZE B	CODE ID 74868	REV AA	ITEM NO.	82-65
							PART NO.	82-65