

## PRO PM 75W 48V 1.6A

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Due to the wide range of variants with output voltages of 5, 12, 24, and 48 V and extensive international approvals, they are suitable for use in many applications. The power range extends from 35 W to 350 W. The individual adaptability makes PRO-PM the right choice for many standard machines.

### General ordering data

|            |   |
|------------|---|
| Version    | Power supply, switch-mode power supply unit |
| Order No.  | <a href="#">2660200284</a>                  |
| Type       | PRO PM 75W 48V 1.6A                         |
| GTIN (EAN) | 4050118782059                               |
| Qty.       | 1 items                                     |

## PRO PM 75W 48V 1.6A

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

### Dimensions and weights

|            |       |                 |             |
|------------|-------|-----------------|-------------|
| Depth      | 99 mm | Depth (inches)  | 3.8976 inch |
| Height     | 30 mm | Height (inches) | 1.1811 inch |
| Width      | 97 mm | Width (inches)  | 3.8189 inch |
| Net weight | 240 g |                 |             |

### Temperatures

|                     |                |                       |                |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -20 °C...70 °C |
| Humidity            | 5...95 % RH    |                       |                |

### Environmental Product Compliance

|                                      |   |
|--------------------------------------|---|
| RoHS Compliance Status               | Compliant with exemption                |
| RoHS Exemption (if applicable/known) | 6c, 7a, 7cl                             |
| REACH SVHC                           | Lead 7439-92-1, Lead monoxide 1317-36-8 |
| SCIP                                 | 015c3a09-4dd7-4b84-85e2-16a46fa4e79a    |

### Input

|  |   |       |  |
|--|---|-------|--|
| Connection system                                    | Screw connection                        |       |  |
| AC input voltage range                               | 90...264 V AC                           |       |  |
| Recommended back-up fuse                             | 4 A at 230 V AC, characteristic curve C |       |  |
| Frequency range AC                                   | 47...63 Hz                              |       |  |
| Rated input voltage                                  | 100...240 V AC                          |       |  |
| AC current consumption                               | 1 A @ 230 V AC / 2 A @ 115 V AC         |       |  |
| Inrush current                                       | max. 45 A                               |       |  |
| Current consumption in relation to the input voltage | Voltage type                            | AC    |  |
|  | Input voltage                           | 230 V |  |
|  | Input current                           | 1 A   |  |
|  | Voltage type                            | AC    |  |
|  | Input voltage                           | 115 V |  |
|  | Input current                           | 2 A   |  |
| Nominal power consumption                            | 87.2 VA                                 |       |  |

### Output

|                                  |   |                                |                        |
|----------------------------------|---|--------------------------------|------------------------|
| Output power                     | 75 W  | Mains failure bridge-over time | 20 ms                  |
| Connection system                | Screw connection  | Rated output voltage           | 48 V DC                |
| Residual ripple, breaking spikes | <150 mVPP   | Parallel connection option     | Yes, with diode module |
| Overload protection              | 120%...180% Inominal, hiccup mode with automatic recovery             | Surge protection               | 55...62 V @ 48 V DC    |
| Output voltage, note             | ± 10% nominal output voltage tolerance, adjustable with potentiometer | Rated current                  | 1.6 A                  |

## PRO PM 75W 48V 1.6A

**Weidmüller Interface GmbH & Co. KG**

 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### General data

|  |                        |                   |                   |
|--|------------------------|-------------------|-------------------|
| Degree of efficiency                   | 86%                    | Humidity          | 5...95 % RH       |
| Protection degree                      | IP20                   | Status indication | LED green: ready  |
| Mounting position, installation notice | Panel mount, screw fix | Derating          | > 50°C (2% / 1°C) |
| Short-circuit protection               | Yes                    |                   |                   |

### EMC / shock / vibration

|                                    |  |   |   |
|------------------------------------|--|---|---|
| Shock resistance IEC 60068-2-27    | 30 g in all directions   | Noise emission in accordance with EN55032 | Class B   |
| Interference immunity test acc. to | Burst: EN 61000-4-4 / ESD EN 61000-4-2, EN61000-4-3 (HF field), EN 61000-4-5 (surge), EN 61000-4-6 (conducted), EN61000-4-8 (Fields), EN 61000-4-11 (Dips) | Vibration resistance IEC 60068-2-6        | 10...500 Hz, constant acceleration 5 g, 10 minutes/cycle, 60 minutes/axis |

### Insulation coordination

|                                   |        |                                  |      |
|-----------------------------------|--------|----------------------------------|------|
| Insulation voltage, input/output  | 3 kV   | Insulation voltage input / earth | 2 kV |
| Insulation voltage output / earth | 0.5 kV |                                  |      |

### Electrical safety (applied standards)

|                          |  |  |  |
|--------------------------|--|--|--|
| Safety extra-low voltage | SELV acc. to IEC 60950-1, PELV according to EN 60204-1 |  |  |
|--------------------------|--|--|--|

### Connection data (input)

|   |                      |   |                   |
|---|----------------------|---|-------------------|
| Connection system                         | Screw connection     | Conductor cross-section, AWG/kcmil , max. | 12 AWG            |
| Conductor cross-section, AWG/kcmil , min. | 21 AWG               | Conductor cross-section, rigid , max.     | 4 mm <sup>2</sup> |
| Conductor cross-section, rigid , min.     | 0.34 mm <sup>2</sup> |   |                   |

### Connection data (output)

|   |                      |   |                   |
|---|----------------------|---|-------------------|
| Connection system                         | Screw connection     | Conductor cross-section, AWG/kcmil , max. | 12 AWG            |
| Conductor cross-section, AWG/kcmil , min. | 21 AWG               | Conductor cross-section, rigid , max.     | 4 mm <sup>2</sup> |
| Conductor cross-section, rigid , min.     | 0.34 mm <sup>2</sup> |   |                   |

### Signalling

|                   |                  |  |  |
|-------------------|------------------|--|--|
| Status indication | LED green: ready |  |  |
|-------------------|------------------|--|--|

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002540    | ETIM 9.0    | EC002540    |
| ETIM 10.0   | EC002540    | ECLASS 14.0 | 27-04-07-01 |
| ECLASS 15.0 | 27-04-07-01 |             |             |