

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1718143003

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 396 RPC Wire-to-Board Right-Angle Header with Friction Lock, 3 Circuits



Series image - Reference only

Documents:	
3D Model	Packaging Specification PK-171814-0001-001 (PDF)
Drawing (PDF)	Test Summary TS-171813-0001-001 (PDF)
3D Model (PDF)	Test Summary TS-171814-0001-001 (PDF)
Product Specification PS-171813-0001-001 (PDF)	Symbol Footprint Data SYM-171814-0003 (PDF)
Product Specification PS-171813-0002-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	171814
Application	Power, Signal, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 396
UPC	887191718224
Physical	
Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-1
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	1.217/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	3.96mm
Plating min - Mating	1.524µm
Polarized to Mating Part	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

171814 Series

Mates With

2145 , 41815 , 6442 , 2139 , 41696

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-171814-0001-001
Product Specification	PS-171813-0001-001, PS-171813-0002-001
Sales Drawing	SD-171814-0001-000, SD-171814-0001-002
Symbol/Footprint Data	SYM-171814-0003
Test Summary	TS-171813-0001-001, TS-171814-0001-001

This document was generated on 02/19/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION