


Cable marker - US-WMTB (24X5) GN - 0829325

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker, Card, green, unlabeled, can be labeled with: THERMOMARK PRIME, THERMOMARK CARD, Mounting type: thread on, Cable diameter: >13 mm, Lettering field: 24 x 5 mm



Why buy this product

- ✓ The US-WMTB... UniSheet labeling range includes markers that can be secured using standard cable binders
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- ✓ The perforated marking strips are easy to separate and can be easily fitted
- ✓ The sheets provide space for including function texts

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 046356 613323
GTIN	4046356613323
Weight per Piece (excluding packing)	12.000 g
Custom tariff number	39204910
Country of origin	Germany

Technical data

Dimensions

Length (b)	24 mm
Width (a)	14 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
---------------------------------	------------------

Cable marker - US-WMTB (24X5) GN - 0829325

Technical data

Ambient conditions

Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in the original packaging is recommended prior to processing.
--------------------------------	---

General

Color	green
Type	Card form
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	35
Number of individual labels per row	7
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
Ink ribbon	5146451 THERMOMARK CARD-US-MAG1
	0801371 THERMOMARK-RIBBON 110-TC
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	thread on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Cable marker - US-WMTB (24X5) GN - 0829325

Classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards

Cable marker - US-WMTB (24X5) GN - 0829325

Accessories

Magazine - TMP-US-MAG1 - 0803341



Magazine for the THERMOMARK PRIME printer, for accommodating US cards

Phoenix Contact 2017 © - all rights reserved
<http://www.phoenixcontact.com>