



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	SEE DETAIL	"A" +/- .062	MARKER ACROSS	TUBING COLOR	MARKERS PER ROLL
H050X084H1T	C	0.50 [ 12.70 ]	4	WHITE	2000
H100X084H1T	A	1.00 [ 25.40 ]	2		1000
H200X084H1T	B	2.00 [ 50.80 ]	1		500
H100X084H2T	A	1.00 [ 25.40 ]	2	YELLOW	1000
H200X084H2T	B	2.00 [ 50.80 ]	1		500
H100X084H3T	A	1.00 [ 25.40 ]	2	BLACK	1000
H200X084H3T	B	2.00 [ 50.80 ]	1		500
H100X084H4T	A	1.00 [ 25.40 ]	2	RED	1000
H200X084H4T	B	2.00 [ 50.80 ]	1		500

10



NOTE:  
1. DIMENSIONS IN ( ) ARE IN MILLIMETERS.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
10	4/30/15	RVU	SEWH	JHAC	ADD NEW COLUMN OF MARKERS PER ROLL.	GAECN02785
9	1/16/15	RVU	SEWH	MSAD	ADD NEW PN, H050X084H1T. ADD NEW DETAIL C WITH 4 COLUMNS FOR H050X084H1T.	GAECN02538
8	4/12/12	RVU			REVISED ON DETAIL A, B, DESIGN TO SHOW ALL MARKERS.	6731
7	12/1/10	RVU			CHANGE BOX DESIGN.	6230
6	5/21/09	RVU			+/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010. HT: .84 +/- .062 WAS .840. MAT'L, HSK TUBING GMUHS31, 3.5 WIDE LINER WAS GMUHS. ADD "A" +/- .062.	5593

TITLE	
<b>H***X084H*T</b> OPTIMUM COMPUTER PRINTABLE MIL. SPEC. HEAT SHRINK MARKERS CUSTOMER DRAWING	
ITEM REVISION NAME	100923NK/13
DATASET FILE NAME	100923NK_DC_C10436/13L
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN ( mm )	
.x ± .12 [ 3.05 ]	.xxx ± .020 [ .508 ]
.xx ± .062 [ 1.57 ]	ANGLES ±
THIRD ANGLE PROJECTION	
MATERIAL:	
HEATSHRINK TUBING GMUHS31, 3.5 WIDE LINER	
DRAWING NUMBER:	
C10436	
DRAWN BY	DATE
RVU	8/2/06
CHK	SCALE
MSAD	NTS
SHT 1 OF 1	
SIZE	
A	