




3RD ANGLE PROJECTION



REMOVE ALL SHARP EDGES AND BURRS

TABLE 1

SHELL SIZE	A MAX	B MAX	C	D	H	MAX ENTRY
1	31,8	13,4	25,0	11,2	21,23	32
2	40,1	13,4	33,3	11,2	29,46	33
3	54,1	13,4	47,0	11,2	43,23	35
4	70,4	13,4	63,5	11,2	59,66	35
5	68,1	16,2	61,1	13,9	57,28	35
6	70,4	17,8	63,5	15,5	60,43	35

TABLE 2A - FOR SHELL SIZES 1 - 4

ENTRY SIZE	J	K	G MAX
16*	4,8	-	26,3
18*	5,2	-	26,3
23*	6,4	-	26,3
30*	7,9	-	26,3
31*	9,5	-	26,3
32*	11,1	-	26,3
33	11,1	22,0	35,3
34	11,1	32,5	45,7
35	11,1	36,0	45,7

TABLE 2B - FOR SHELL SIZES 5 AND 6

ENTRY SIZE	J	K	G MAX SHELL #5	G MAX SHELL #6
16*	4,8	-	28,6	30,1
23*	6,4	-	28,6	30,1
30*	7,9	-	28,6	30,1
31*	9,5	-	28,6	30,1
32*	11,1	-	28,6	30,1
33*	14,3	-	28,6	30,1
34	14,3	27,0	45,7	45,7
35	14,3	31,8	45,7	45,7

* - CIRCULAR ENTRY STYLE TO ØJ

NOTES:


1. PLATING
B - CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
C - ELECTROLESS NICKEL
ZB - ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL

FOR COMPLETE PLATING OPTIONS AND SPECS. PLEASE CONTACT THE SALES OFFICE

2. PROVIDED WITH STANDARD BAND

100P2497B-3 33 0 0 -1-C-PH

- SERIES
ENTRY POSITION (B - 45° ENTRY)
SHELL SIZE (TABLE 1)
ENTRY SIZE (TABLE 2A AND 2B)
SLOT OPTION (SEE SHEET 2, TABLE 3)
(0 {ZERO} - NO SLOT)
(S - SLOT INCLUDED)
TY-POST OPTION (SEE SHEET 2)
(0 {ZERO} - NO TY-POST)
(T - TY-POST INCLUDED)
MATERIAL (1 - ALUM ALLOY)
PLATING (SEE NOTE 1)
PH - POLAMCO HARDWARE
(HEX SOCKET HEAD JACKSCREW)
OMIT FOR STANDARD HARDWARE




DIMENSIONS APPLY AFTER PLATING

ISSUE	DCR NO.	DATE	APPROVED	MATERIAL	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES TOLERANCE ON DIMENSIONS +/-0.1MM TOLERANCE ON ANGLES +/- 1 DEGREE	DO NOT SCALE THIS DRAWING	POLAMCO LTD	PART NO
4	4698	29/03/2012	MXF	ALUM ALLOY		THIS DRAWING IS COPYRIGHT, AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	100P2497B SERIES
								ASSY USED ON
								MIL-DTL-24308
								DRAWING NO
								P9179



SLOT OPTION



TY-POST OPTION




TABLE 3

ENTRY SIZE	L
16	4,8
18	5,1
23	5,6
30	6,4
31	7,1
32	7,9
33	9,7
34	11,2
35	11,4

DIMENSIONS APPLY AFTER PLATING

ISSUE	DCR NO.	DATE	APPROVED	MATERIAL ALUM ALLOY	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES TOLERANCE ON DIMENSIONS +/-0.1MM TOLERANCE ON ANGLES +/- 1 DEGREE		DO NOT SCALE THIS DRAWING	POLAMCO LTD WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PART NO 100P2497B SERIES
4	4698	29/03/2012	MXF				THIS DRAWING IS COPYRIGHT, AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.		TITLE D-SUB BANDING ADAPTOR
					WEIGHT				
				NCAGE CODE: U5792	DRAWN	DIW			DRAWING NO P9179