






PRODUCT NUMBER SEE SHEET 2



spec ref	*	dr	Peng-Bing Fu	2012/10/31	projection	MM	size	A3	scale	3:2
tolerance std	ASME Y14.5	eng	Peng-Bing Fu	2013/03/12	chr	-	ecn no	-	rel level	Released
surface	✓	appr	Pei-Ming Zheng	2013/03/12	product family	PwrBlade+	rel level	Released	rev	A
linear	0.X	±0.5	FCI	12HP + 24S	cat. no.	Product - Customer Drw	sheet 1 of 3			
linear	0.XX	±0.25		RA STB RECEPTACLE						
linear	0.XXX	±0.10								
angular	0°	±2°	www.fci.com							

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
 - HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
 - SIGNAL CONTACT - COPPER ALLOY.
 - POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- 9) THE VOID CORING IN BETWEEN POWER MODULES, SIGNAL
MODULES AND END MODULES ARE OPTIONAL AND THE SHAPE
MAY BE DIFFERENT FOR OPTIMIZE THE MOLDING PROCESS. THE
VOID CORING WILL NOT EFFECT TO PRODUCT FUNCTION.

dr	Peng-Bing Fu	2012/10/31	projection 	MM 	size	scale
eng	Peng-Bing Fu	2013/03/12			A3	3:2
chr	-	-			ecn no	-
appr	Pei-Ming Zheng	2013/03/12	product family	PwrBlade+	rel level	Released
www.fci.com		title			dwg no	rev
		12HP + 24S RA STB RECEPTACLE			10106126-C006001	A
cat. no.		Product - Customer Drw			sheet 3 of 3	