

Data sheet

PT11AxxVBBN Typ 220

Page 1/6

P/N
312202xx

xx=number of poles


2019/10/28

Version: N


Illustrations



Dimensional drawing



Drill pattern



See enlarged drawings at the end of document

Product specification

- pin header, solderable
- centerline 10.16 mm, direction of connection vertical 0°
- closed ends
- color black



Data sheet

PT11AxxVBBN Typ 220

Page 2/6

P/N
312202xx

xx=number of poles

2019/10/28

Version: N

Technical Data

General Data

Solder pin length	3.25 mm		
min. number of poles	2		
max. number of poles	12		
Insulating material class	CTI 600		
clearance/creepage dist.	9.18 mm		
protection category	IP00		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	630 V	1000 V	1000 V
Rated test voltage	8 kV	8 kV	8 kV

Approvals

 V / A	600 / 15
approval UL - File No.	E121004
 1.5 mm ²	630 V / 6 kV / 13.5 A / 1.0 x 1.0 mm

Material

insulating material	PA66
flammability class	V0
contact pin material	CuFe
contact pin surface	Ni + Ag
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12
Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13
REACH - substance (SVHC)	none

Climatic Data

upper limit temperature	105 °C
lower limit temperature	-40 °C

General

Tolerance	ISO 2768 -mH
Solderability	Acc. to JEDEC JESD22-B102E 245°C/5s

U | Contact

Data sheet

PT11AxxVBBN Typ 220

Page 3/6

P/N

312202xx

xx=number of poles

2019/10/28

Version: N

Accessories

P/N	Designation
700024-01-9	700024

U | Contact

Data sheet

PT11AxxVBBN Typ 220

Page 4/6

P/N

312202xx

xx=number of poles

2019/10/28


Version: N

Counterpart of

P/N	Designation
312132	RP03AxxHBLC Typ 213
312142	RP03AxxHBLD Typ 214
312502	RP01AxxSBLC Typ 250
ASP04A	SP04AxxVBNC ASP04A

Illustrations

Dimensional drawing



$L = (\text{pole size} - 1) \times \text{centerline} + 6.28 \text{ mm} [0.247]$



Illustrations

Drill pattern

