



Part Number : [16020111](#)

Product Description : SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 36-32 AWG, Bag

Series Number : 70021

Status : Active

Product Category : Crimp Terminals

Engineering Part Number : 70021-0213



Documents and Resources

Drawings

[016020111 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-70021-001.pdf](#)

[PS-70400-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	70021
Description	SL Crimp Terminal, Series 70021, Male, 8.43mm Mating Length, Tin (Sn) Plated, 36-32 AWG, Bag
Application	Signal, Wire-to-Wire
Product Name	SL
UPC	800753775220

Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.102/g
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.64mm max.
Wire Size (AWG)	32, 34, 36

Wire Size mm ²	N/A
---------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings and CPA Retainers	<u>70066</u>
SL Single Row Crimp Housings	<u>70107</u>

Application Tooling

Global

Description	Part Number
Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals	<u>11020022</u>
PremiumGrade Hand Crimp Tool for SL Crimp Terminals, 24-22 AWG and 36-32 AWG	<u>638118700</u>

This document was generated on Apr 27, 2026