


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	RELEASE	28MAR16	JAH	KING








M12 A-CODED
5P FEMALE



TECHNICAL DATA:

1) CONNECTOR MATERIALS
   - COUPLING NUT: THERMOPLASTIC, NYLON, UL94 V-0
   - INSULATION INSERT: THERMOPLASTIC, NYLON, UL 94V-0
   - MACHINED CONTACT: GOLD FLASH PLATING OVER COPPER ALLOY
   - PREMOLD MATERIAL: HOTMELT
   - OVERMOLD MATERIAL: THERMOPLASTIC, PVC COLOR: GRAY
   - WIRE:UL1007 22AWG 105C° 300V, PVC
   - LED: GALLIUM PHOSPHIDE
2) RoHS COMPLIANT
3) CONNECTOR SPECIFICATION
   - VOLTAGE RATING: 12V
   - CONTACT RESISTANCE: ≤ 5 mΩ
   - PROTECTION CLASS: IP67
   - OPERATING TEMPERATURE: -25°C~90°C

WIRING DIAGRAM



CUSTOMER DRAWING

	PART NUMBER	DESCRIPTION	ITEM
QUANTITY	MATERIALS LIST		

UNLESS OTHERWISE SPECIFIED
1) All dimensions are in metric(mm).
2) Tolerances are as follows:
1 PL DEC ±1.27 | Fractions ±0.40
2 PL DEC ±0.25 | Angles ±1°
3 PL DEC ±0.127
3) FABRICATION STANDARDS PER: S5-20020
4) Note reference = X
L

MATERIAL SPECIFICATIONS:
NOTED

PROCESS SPECIFICATIONS:
IPC/WHMA-A-620

NEXT ASSY:

SIGNATURES		DATE
DRAWN:	FLAN	2015-8-13
CHECKED:	CHELSEA	2015-8-13
ENGINEER:		
APPROVAL:	KING	2015-8-13
CUSTOMER:		

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

Amphenol

Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township, MI 48036

MULTI-HUB TERMINATOR PLUG, NMEA 2000
FEMALE SOCKET W/ L.E.D.

SIZE	FSCM NO	DWG NO:	REVISION
A4	C	AM-N05S-TERM	A1

SCALE: NONE | AM-N05S-TERM | SHEET 1 OF 1

TITLE: MULTI-HUB TERMINATOR PLUG NMEA 2000, FEM. SOCKET W/ LED | DWG NO: AM-N05S-TERM | REV: A1 | SH: 1 | OF: 1

Downloaded from Arrow.com.