





PRODUCT NUMBER	PITCH
YExx01x000J0G	5.00 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW



Material:

- Item **a** Terminal housing: Thermoplastic (UL 94V-0)
- Item **b** Clamp: Brass, Ni plated
- Item **c** Solder pin: Brass, Tin plated
- Item **d** Terminal screw: Steel, Zinc plating"- "slot type

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:

DIMENSION

Dim L	$N \times 5.0$
Dim B	$(N-1) \times 5.0$

N=Number of poles

Poles	Tolerance
2p~6p	± 0.15
7p~12p	± 0.25
13p~18p	± 0.35
19p~24p	± 0.40

PART NO.: YE xx 0 1 x 0 00J0 G

		Color	RoHS compliant (lead<4%)
End stackable	0	Black (RAL9005)	In copper Alloy
No. of poles	2	Red (RAL3001/D)	
02 2 poles	3	Orange(RAL2011/P)	
03 3 poles	4	Yellow(RAL1018/A)	
... ..	5	Green(RAL6018/T)	
24 24 poles	6	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

[illegible]