



Part Number : [1200878798](#)
Product Description : Micro-Change (M12) to Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 4 Poles, Female (Straight) to Male (Straight), 24 AWG, WSOR Cable, 10.0m (32.81') Length
Series Number : 120087
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 484030B41M100



Documents & Resources

Drawings

[1200878798_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120087
Description	Micro-Change (M12) to Nano-Change (M8) Double-Ended Cordset with Knurled Hexnut, 4 Poles, Female (Straight) to Male (Straight), 24 AWG, WSOR Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Micro-Change (M12), Nano-Change (M8)
Protocol	N/A
Type	Double Ended
UPC	889056132633

Electrical

Current - Maximum per Contact	3.0A, 4.0A
Voltage - Maximum	30V

Physical

Cable Diameter	4.80mm (.189")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)

Connector End B	Nano-Change (M8)
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	333.862/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	WSOR
Wire Size (AWG)	24

This document was generated on Sep 11, 2025