



Technical Data

17.08.2021

Heat shrinkable tubing 2:1 - flexible and coloured
HFT-A - self extinguishing

HFT-A-2.4/1.2

Article Number 305-02409



Material: Polyolefin, cross-linked (PO-X)
Colour: White (WH)

Supplied $\varnothing$ D min.: 2.4 mm
Recov. $\varnothing$ d max.: 1.2 mm
Wall (WT): 0.50 mm
Shrink Ratio: 2:1
Longitudinal Change After Shrinkage: -5 % max.
Min. Shrink Temperature - °C: +135 °C

Test Method

Flammability: self-extinguishing, UL 224 VW-1
Operating Temperature - °C: -55 °C to +135 °C
Heat Shock Test: 4h/200°C
Tensile Strength at Heat Shock: 13 MPa
Elongation at Heat Shock: 390 %
Behaviour At Low Temperature: not cracking

IEC 60684-2

Dielectric Strength: >21 kV/mm IEC 60684-2
Insulation Class: B (VDE 0530)
Tensile Strength: 14 MPa IEC 60684-2
Elongation at break: 400% IEC 60684-2
Specifications: ANSI/UL 224, CLASS 903201, VG 95343-5:2016-10



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved