



Part Number : [2138800003](#)
Product Description : Sentrality 11.0mm Bottom-entry, Surface Mount Socket Assembly with +/-1.00mm Self-alignment Capability, Tape and Reel
Series Number : 213880
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[2138800003_sd.pdf](#)
[2138800001-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[2138800001-AS-000.pdf](#)
[2138800001-PS-000.pdf](#)
[2138800001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	213880
Description	Sentrality 11.0mm Bottom-entry, Surface Mount Socket Assembly with +/-1.00mm Self-alignment Capability, Tape and Reel
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar, Power
Comments	Current and voltage performances are dependent upon application variables.
Component Type	PCB Receptacle
Product Name	Sentrality
UPC	195842267381

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	300.0A
-------------------------------	--------

Voltage - Maximum	600V
-------------------	------

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1
Diameter	11.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Height Above Board	5.17mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver
Mating Orientation	Bottom-entry
Net Weight	10.120/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Retention	None
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality 11.00mm Screw Mount Pins	<u>213902</u>