



**Part Number :** [1727040134](#)

**Product Description :** FCT High Voltage Contact, Male, Straight, Solder Cup, 1.30µm Gold Mating Plating, with Plastic Retention Clip, 2.0A, 20 AWG or smaller

**Series Number :** 172704

**Status :** Active

**Product Category :** D-Sub Contacts

**Engineering Part Number :** FMV001P107K

---

## Documents and Resources

### Drawings

[1727040134\\_sd.pdf](#)

### Specifications

[1731120009-PK-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 3; 34; 33
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025) SCIP:908c72f7-97f6-4a9e-b041-d95f23d9b169
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	D-Sub Contacts
Series	172704
Description	FCT High Voltage Contact, Male, Straight, Solder Cup, 1.30µm Gold Mating Plating, with Plastic Retention Clip, 2.0A, 20 AWG or smaller
Contact Type	High Voltage
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056020459

### Electrical

Current - Maximum per Contact	2.0A
-------------------------------	------

### Physical

Durability (mating cycles min)	500
Gender	Male
Material - Contact	Copper Alloy
Material - Insulator	PTFE
Material - Plating Mating	Gold over Nickel
Material - Retaining Clip	PEI

Net Weight	0.700/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	1.300µm
Temperature Range - Operating	-55° to +125°C
Termination Style	Solder Cup
Wire Size (AWG)	20

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
FCT High Voltage Contact, Female, Straight, Solder Cup, 1.30µm Gold Mating Plating, with Plastic Retention Clip, 2.0A, 20 AWG or smaller	<a href="#"><u>1727040135</u></a>

### Use with Part(s)

Description	Part Number
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 9 Circuits Max, 5 Signal Contacts Loaded, Green Insulator	<a href="#"><u>1731070061</u></a>
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 7 Circuits Max, 5 Signal Contacts Loaded, Green Insulator	<a href="#"><u>1731070059</u></a>
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 24 Circuits Max, 17 Signal Contacts Loaded, Green Insulator	<a href="#"><u>1731070069</u></a>
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder	<a href="#"><u>1731070102</u></a>

Cup, Gold Plating, Tin-plated Shell with Dimples, 11 Circuits Max, 10 Signal Contacts Loaded, Green Insulator	
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold over Nickel Phosphorus Plating, Tin-plated Shell with Dimples, 11 Circuits Max, 10 Signal Contacts Loaded, Green Insulator	<u>1727040011</u>
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 27 Circuits Max, 25 Signal Contacts Loaded, Green Insulator	<u>1731070112</u>
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 5 Circuits Max, 4 Signal Contacts Loaded, Green Insulator	<u>1731070363</u>
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 17 Circuits Max, 15 Signal Contacts Loaded, Green Insulator	<u>1731070065</u>
FCT Mixed Layout D-Sub Connector, Male, Straight, Solder Cup, Gold Plating, Tin-plated Shell with Dimples, 21 Circuits Max, 17 Signal Contacts Loaded, Green Insulator	<u>1731070067</u>

---

## Application Tooling

### Global

Description	Part Number
FCT Removal Tool for Size 8	<u>1731121747</u>

---

This document was generated on Apr 11, 2026