

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	ECR-20-004655	06OCT20	RK	SBH


NOTE:

1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND
2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO
TE-SPEC.108-18857, SUBSECTION 3.1.1
3. ASSEMBLY COLOR: WHITE

4 KEYING HV-2 AND HV-4 AS SHOWN

PN	KEYING
1--X	HV-4
2--X	LV-2

PN	L	TOLERANCES/mm
X-2083074-1	610mm (2ft)	+/- 5
X-2083074-2	1270mm (4ft)	+/- 15
X-2083074-3	1880mm (6ft)	+/- 20
X-2083074-4	2490mm (8ft)	+/- 20
X-2083074-5	3100mm (10ft)	+/- 30
X-2083074-6	3660mm (12ft)	+/- 30
X-2083074-7	4270mm (14ft)	+/- 50
X-2083074-8	4880mm (16ft)	+/- 50





PC	AR	AR	Cable SVT 2xAWG18 UL WH	4
PC	2	2	MICRO QUADLOK SYSTEM SOCKET CONTACT	3
PC	1	1	TUBE FOR SVT CABLE	2
PC	—	1	PLUG MINI HVL HV-4	1
PC	1	—	PLUG MINI HVL HV-2	
UOM	QTY	QTY	DESCRIPTION	POS.
	2--X	1--X		

1 2 3 4

OBSOLETE

PC
PC
PC
PC
PC
UOM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SATHISH KUMAR.G		<div> TE Connectivity</div>							
		CHK R.HOSSAINI									
DIMENSIONS: mm		APVD R.HOSSAINI		NAME CABLE ASSEMBLY NECTOR S LINE 2POS. HV-2 AND HV-4							
		PRODUCT SPEC —									
		APPLICATION SPEC —									
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		WEIGHT —		SIZE A3		CAGE CODE 00779		DRAWING NO C-2083074		RESTRICTED TO —	
MATERIAL —		FINISH —		CUSTOMER DRAWING							
				SCALE NTS		SHEET 1 OF 1		REV D1			