


COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology, full LTE, NEMP tested
3400.41.0266

Properties

- Full Band LTE Protector
- NEMP tested
- Highest current handling capability up to 100 kA max.
- Maintenance free
- Best PIM performance



Product configuration	
Main path connectors	Port 1: unprotected, 7/16 plug (male) Port 2: protected, 7/16 jack (female)
Mounting and grounding	MH110 (bulkhead mounting), M8 (screw), brk (bracket)
Side of bulkhead	protected side
EMP can be install reversed	YES

Interface and material data	
Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Brass / Silver Plating Port 2: Bronze / Silver Plating

Electrical data	
Impedance	50 Ω
Frequency frame	690 MHz to 2690 MHz
Return loss typical	≥ 28 dB
Insertion loss typical	≤ 0.1 dB
CW power frame	≤ 1500 W
PIM 3rd order	-160 dBc max.
AISG insertion loss	0.1 dB
Residual pulse energy (typ.)	11 μJ LEMP (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
	270 μJ NEMP (test pulse 6 kV 5/200 ns)
	21 mJ (test pulse 100 kA 8/20 μs)
	2.5 mJ (test pulse 25 kA 10/350 μs)
Residual pulse voltage (typ.)	12 V LEMP (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
	650 V NEMP (test pulse 6 kV 5/200 ns)
	285 V (test pulse 100 kA 8/20 μs)
	80 V (test pulse 25 kA 10/350 μs)
Surge current handling capability	100 kA single, 80 kA multiple (test pulse 8/20 μs)

COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology, full LTE, NEMP tested
3400.41.0266

Electrical remarks	
Gas tube	No DC / shorted QW or LC

Mechanical data	
Weight	490 g
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP67, according to IEC 60529
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. A
Moisture resistance according	MIL-STD-202, Method 106

Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84143443	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table	
Item number	Item description
84143443	3400.41.0266

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2047 / Date of publication: 28.02.2025 / uncontrolled copy