





10. TE TESTING PER 108-163023 PENDING.

LP CONFIGURATION TAIL DIMENSIONS

Downloaded from Arrow.com.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

PART NUMBER	ROWS	POWER					SIGNAL								POWER		
		P6	LP2	P5	P4	P3	8	7	6	5	4	3	2	1	LPI	P2	PI
2313441-1	D						AP	AP	AP	AP	AP	AP	AP	AP			
	C						AP	AP	AP	AP	AP	AP	AP	AP			
	B	GS	LSI	GS	GS	GS	AP	AP	AP	AP	AP	AP	AP	AP	LSI	GS	GS
	A						AP	AP	AP	AP	AP	AP	AP	AP			
2ACP + 1LP + 32S + 3HDP + 1LP + 1P																	



RECOMMENDED PCB LAYOUT

LSI	LOW POWER PRESS FIT CONTACTS .135 [3.43] TAIL LENGTH
GS	STD POWER PRESS FIT CONTACT .135 [3.43] TAIL LENGTH
AP	SIGNAL PRESS FIT CONTACT .135 [3.43] TAIL LENGTH
CODE	TAIL LENGTH
CONTACT TABLE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. MILLER 28MAR2018	NAME MULTIBEAM 270V, VERT ASSY VITA 62.2 3U J0, PRESS FIT	
DIMENSIONS: INCHES [mm]		CHK N. RUFFINI 28MAR2018		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	PRODUCT SPEC 108-163023	RESTRICTED TO
MATERIAL -		APPLICATION SPEC 114-13251	SIZE A1	REV 1
FINISH -		WEIGHT -	CAGE CODE 00779	SCALE 2:1
CUSTOMER DRAWING		DRAWING NO 2313441		SHEET 2 OF 2