

**ZAP/TW 1 OR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

|            |                                      |
|------------|--------------------------------------|
| Version    | Z-series, End plate, Partition plate |
| Order No.  | <a href="#">1608760000</a>           |
| Type       | ZAP/TW 1 OR                          |
| GTIN (EAN) | 4008190190873                        |
| Qty.       | 50 pc(s).                            |

Creation date May 24, 2025 6:20:37 AM CEST

Catalogue status 10.05.2025 / We reserve the right to make technical changes.

## ZAP/TW 1 OR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 30.5 mm | Depth (inches)  | 1.201 inch |
| Height     | 59.5 mm | Height (inches) | 2.343 inch |
| Width      | 2 mm    | Width (inches)  | 0.079 inch |
| Net weight | 2.894 g |                 |            |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C        |

## Material data

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | orange |
| UL 94 flammability rating | V-0   |        |        |

## System specifications

|         |                            |
|---------|----------------------------|
| Version | End and intermediate plate |
|---------|----------------------------|

## Additional technical data

|                     |                 |         |     |
|---------------------|-----------------|---------|-----|
| Installation advice | Direct mounting | Snap-on | Yes |
|---------------------|-----------------|---------|-----|

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ETIM 10.0   | EC000886    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-33 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |
| ECLASS 13.0 | 27-25-03-01 | ECLASS 14.0 | 27-25-03-01 |
| ECLASS 15.0 | 27-25-03-01 |             |             |

Cradle to gate

0.037 kg CO2eq.

## Environmental Product Compliance

|                          |                                               |
|--------------------------|-----------------------------------------------|
| RoHS Compliance Status   | Compliant without exemption                   |
| REACH SVHC               | No SVHC above 0.1 wt%                         |
| Product Carbon Footprint | de.myview.objectmodel.impl.BlockImpl@61278789 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## ZAP/TW 1 OR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Confirmation of Standards EN 45545-2\\_2020-10](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)