



**HARNESSING**

END CAPS



✓ Active

TE CONNECTIVITY (TE)

**101A041-3/42-0**

Raychem | CAP , CRPS

101A041-3/42-0

TE Internal Number: 843338-000

Alias ID: 6-1197930-8

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

**Product Type** End Cap

**Adhesive Type** General Purpose Pre-Coat Adhesive

**Expanded Inside Diameter (Min)** 13.7 mm [ .54 in ]

**Recovered Inside Diameter (Max)** 6.4 mm [ .25 in ]

**Material** Modified Polyolefin

[↓ PRODUCT DRAWING](#)  
English

## DOCUMENTATION

Product Drawings

**Cap, Round End**

PDF

**English**

Product Specifications

Product Specification

**Thermofit Polyolefin Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable**

PDF

**English**

Product Environmental Compliance

Safety Data Sheet

**Aliphatic Polyamide Based Adhesives.**

PDF

**Dutch**

**Aliphatic Polyamide Based Adhesives.**

PDF

**English**

**Aliphatic Polyamide Based Adhesives.**

PDF

**French**

**Aliphatic Polyamide Based Adhesives.**

PDF

**German**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Italian**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Spanish**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Swedish**

**Aliphatic Polyamide Based Adhesives.**

PDF

**English**

**EPS Heat Shrinkable Polymeric Products**

PDF

**French**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Italian**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Norwegian**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Danish**

**EPS Heat Shrinkable Polymeric Products**

PDF

**English**

**EPS Heat Shrinkable Polymeric Products**

PDF

**German**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Spanish**

**EPS Heat Shrinkable Polymeric Products**

PDF

Swedish

## EPS Heat Shrinkable Polymeric Products

PDF

Dutch

### FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

#### Product Type Features

**Product Type** End Cap

**Size Code** 41

#### Body Features

**Material** Modified Polyolefin

**Pliancy** Semi-Rigid

**Adhesive Pre-Coat** Yes

**Material Code** 3

#### Dimensions

**Expanded Inside Diameter (Min)** 13.7 mm [ .54 in ]

**Recovered Inside Diameter (Max)** 6.4 mm [ .25 in ]

**Length** 40 mm [ 1.572 in ]

**Recovered Wall Thickness (Nominal)** 1.78 mm [ .07 in ]

#### Usage Conditions

**Operating Temperature Range (°C)** -20 – 60

**Resistance Protection** Suitable for occasional exposure to fluids

#### Industry Standards

**Government Qualified** No

#### Other

**Adhesive Type** General Purpose Pre-Coat Adhesive

**Adhesive Code** 42

#### Statement of Compliance

**Statement of Compliance**

PDF