


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S2	REVISED PER ECR-24-201941	13MAR2024	DB	RE

D


C

B

A



- 1 CONTINUOUS STRIP ON REELS.
- 2 TIN PLATE 0.00381 [.000150] MIN OVER 0.00254 [.000100] MIN THK COPPER OR TIN PLATE 0.00381 [.000150] MIN OVER 0.00127 [.000050] MIN THK NICKEL.
- 3 REELED WITH INTERLEAVING PAPER
- 4 OPTIONAL ID MARK, LOCATED APPROX AS SHOWN.
- 5 PRELIMINARY — NOT FOR PRODUCTION



OBSOLETE	STANDARD	BRASS, SPECIAL HARD	63824-8
	3 STANDARD	BRASS	63824-5
	REVERSE	BRASS	63824-3
	STANDARD	BRASS	5 63824-2
	STANDARD	BRASS	63824-1
	REELING	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

SEE TABLE

FINISH

2

DWN JR RUTH 20FEB01
CHK MS FEHER 20FEB01
APVD N DEIBERT 20FEB01
PRODUCT SPEC
APPLICATION SPEC 114-2115
WEIGHT 0.000000

TE Connectivity

TAB, FASTON, P.C.BOARD 6.35 [.250]

SIZE A3 CAGE CODE 00779 DRAWING NO C-63824

RESTRICTED TO

CUSTOMER DRAWING

SCALE 8:1 SHEET 1 OF 1 REV S2