



C2G
Discontinued - 16.4ft (5m) LC-LC 62.5/125 OM1 Duplex Multimode Fiber Optic Cable (TAA Compliant) - Orange
Part No. 11106



With LC to LC termination, this high quality fiber optic patch cable is specifically designed for fast ethernet, fiber channel, Infiniband®, ATM and gigabit ethernet applications. The small LC connectors satisfy the need for higher port density both in the telecom room and the work area, and offer twice the port density of traditional SC and ST fiber connectors. The LC connector with its RJ-style latch clip design is easy to engage and disengage, and gives each connection greater durability in resisting pulls, strains, snags, and impacts during cabling installs and maintenance.

The patented injection molding process provides each connection greater durability in resisting pulls, strains and impacts from cabling installs.

Each cable is 100% optically inspected and tested for insertion loss before you receive it. A pull-proof jacket design surrounds the popular 62.5/125 multimode fiber, immune to electrical interference.

Features & Benefits

Designed to support gigabit ethernet, fibre channel, ATM, or any application that requires high speed data transfer	Patented injection molding process for greater durability
Optically inspected and tested for insertion loss	Pull-proof jacket design, immune to electrical interference

Specifications

General Info			
Product Line	C2G	Color	Orange
UPC Number	757120111061	Country Of Origin	Hong Kong
Application Sector	Commercial, Industrial	Warranty Type	Lifetime
Type	Cable		
Dimensions			
Product Length US	16.4 FT	Cable Length	16.4 ft
Trade Programs			
TAA Compliant	Yes		
Technical Information			
Fiber Optic Cable Type	Multimode, OM1	Jacket Material	PVC (Polyvinyl Chloride)
Bend Radius	50 mm	Simplex/Duplex	Duplex
Cable Type	Fiber Optic	Jacket Rating	Standard / Non-Rated
Data Transfer Rate	1 Gbps	Connector 2	LC Male
Connector 1	LC Male	Fiber Size	62.5/125