

# SPECIFICATION CONTROL DRAWING

55PC1842


TITLE

FOUR CONDUCTOR CABLE, SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT

Date  
6-10-11

Revision  
B

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.



PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET WALL	LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC1842-24-*	24	38	.0060	.0080	.128	.145	.162	16.81	17.51
55PC1842-22-*	22	38	.0060	.0080	.141	.160	.180	21.61	22.40
55PC1842-20-*	20	38	.0065	.0085	.161	.183	.205	29.35	30.24
55PC1842-18-*	18	38	.0065	.0085	.182	.209	.235	40.32	41.46
55PC1842-16-*	16	38	.0070	.0090	.201	.230	.259	49.42	50.78
55PC1842-14-*	14	38	.0075	.0095	.236	.273	.310	71.85	74.92
55PC1842-12-*	12	36	.0080	.0100	.283	.327	.370	107.32	109.83
55PC1842-10-*	10	36	.0080	.0100	.299	.363	.427	158.39	163.67
55PC1842-8-*	8	34	.0080	.0100	.426	.520	.614	286.71	295.75

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.

Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx".) OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

Page 1 of 2

Raychem, TE Connectivity, TE connectivity (logo) and TE (logo) are trademarks.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.  
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



Raychem Wire & Cable  
501 Oaksider Avenue  
Redwood City, CA 94063-3800  
Phone: 1-800-227-8816  
Fax: 1-650-361-6297

© 2009-2011 Tyco Electronics Corporation., All rights reserved.



# SPECIFICATION CONTROL DRAWING

Page 2 of 2	Revision B	SCD 55PC1842
-------------	---------------	-----------------

## CABLE RATINGS AND ADDITIONAL REQUIREMENTS

### TEMPERATURE RATING: 200°C

Maximum continuous conductor temperature

### VOLTAGE RATING: 600 volts (rms) at sea level

### CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

### DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz

### JACKET COLOR: White preferred

### JACKET ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)

### JACKET FLAWS:

Spark Test, 1000 volts (rms)

Impulse Dielectric Test, 6.0 kV (peak)

### SHIELD COVERAGE: 85% (minimum)

### VOLTAGE WITHSTAND TEST (Post Environmental):

1000 volts (rms), 60 Hz, 1 minute

### PART NUMBER:

The "\*" in the part numbers on page 1 shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color. Colors shown do not necessarily reflect the sequence of manufacturing.

1/ Example: AWG 22, red, yellow, green and blue component wires; white jacket:  
55PC1842-22-2/4/5/6-9

1/ See footer section on page 1