

BMMN000606151R2MX2

Search by :

Part Number

Characteristics

Cross reference



MP



Closed Magnetic Circuit Type
Molding Processing & for Ultra High Current

Series Pdf



Product detail

L(mm) ±	6.47±0.25
W(mm) ±	6.86±0.38
T(mm) ±	1.5Max.
Inductance(uH)	1.2
Tolerance(±%)	20
Test Frequency	100kHz,0.25V
RDC(Ω)Max	0.03
RDC(Ω)Typ	0.025
Isat(A)Typ	8.5
Irms(A)Typ	5.4
Operating Temperature	−55℃~125℃(Including self - temperature rise)


Part Numbering

Dimensions

Packing

Recommended Pattern

Electrical Characteristics



Products

- Power Inductor
- EMI-Common Mode Choke
- EMI-Bead
- RF-Signal Inductor
- RF-Passives/Antennas
- LAN Transformer
- Resistor & Current Sensor

Applications

- Automotive
- Industrial
- Server/DataCenter
- Communication
- Mobile and Tablet
- Computer/Laptop
- Consumer

Design Tools

- Simulation Tool
- Product Search Engine
- E-Catalogue

About Us

- Corporate Overview
- Corporate Milestones
- Core Technology
- Certificates & Awards
- Quality and Social Responsibility

Investor

- Financial Information
- Corporate governance
- Stakeholder Contacts

[Media Center](#)
[New Products](#)
[Events](#)
[Product Notices](#)

Contact Us

[Contact Info](#)
[Contact Form](#)
[Join Chilisín](#)

[Terms of Use](#)
[Privacy policy](#)
[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisín. All rights reserved.