


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED(ECR-11-025980)	16.OCT.12	WY	HG
	B1	REVISED(ECR-15-018591)	22.DEC.15	WY	HG
	C	REVISED(ECR-16-007243)	09.JAN.17	WY	KT
	C1	REVISED(ECR-23-184416)	21082023	JY	KT










TABLE 1.

CONTACT	PART NO.	WIRE SIZE(SQ)
.025 TH	2005098-1	0.13~0.22
	2005154-1	0.3~0.5
	2005154-2	0.5
.060	2109005-1	0.22~0.35
	2109005-2	0.5~0.75
	2109005-3	0.85~1.25
MCP 2.8	2-964292-1	0.35~0.5
	2-964294-1	0.5~1.0
	2-964296-1	1.25~2.5

NOTE,
1. GENERAL TOLERANCE : ±0.3, ±3°
2. CONDITION OF DELIVERY : DBL PLATE IN OPEN POSITION.
3. APPLIED RECEPTACLE CONTACT P/N:SEE TABLE 1
4. SUITABLE MATING PLUG P/N : 2109520
5. SUITABLE MATING CLIP P/N : 368260
6. WARPAGE: MAX 0.4

NO	FINISH/ COLOR	MATERIAL	DESCRIPTION	Q`TY		
				ASS`Y P/N	2109517-6	2109517-3	2109517-1
2	NATURAL	PBT	25P DBL HSG	1	1	1
1	C1 RED	PBT	25P CAP HSG	1	-	-
	GRAY			-	1	-
	NATURAL			-	-	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ± SEE NOTE
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL SEE NOTE

FINISH

DWN WY JANG
CHK YH MA
APVD KT LIM
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME 025/060/110 HYB 25P CAP ASSY

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C- 2109517	

SCALE 1:1 SHEET 1 OF 1 REV C1

1470-19 (3/13)

Printed on 21 Aug 2023 09:55 (???? ???) from FC001820

Downloaded from Arrow.com.