
Part Number : 5051520700
Product Description : DuraClik Wire-to-Board 2-Way Terminal Position Assurance (TPA) Retainer, 7 Circuits
Series Number : 505152
Status : Active
Product Category : Connector Accessories



Documents and Resources

Drawings

5051520700_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-505151-002-001.pdf

AS-505151-001-001.pdf

SPK-505152-001-001.pdf

5051510002-000.pdf (Gold Plating)

PS-505151-001-001.pdf (Tin Plating)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	505152
Description	DuraClik Wire-to-Board 2-Way Terminal Position Assurance (TPA) Retainer, 7 Circuits
Application	Automotive
Component Type	Terminal Position Assurance (TPA)
Product Name	DuraClik
UPC	887191735191

Electrical

Current - Maximum per Contact	3.0A

Physical

Circuits (Loaded)	7
Circuits (maximum)	7
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	84.800/mg
Number of Rows	1
Packaging Type	Bag

Downloaded from Arrow.com.

Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Crimp or Compression

Mates With / Use With

Use with Part(s)

Description	Part Number
DuraClik TPA Single Row Receptacle Housings	505151
DuraClik TPA Female Crimp Terminals	505153

Downloaded from Arrow.com.