

CK1,6-ED-0,37BU AU - Crimp contact



1674969

<https://www.phoenixcontact.com/us/products/1674969>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 0.14 mm² ... 0.37 mm², AWG 26 ... 22

Commercial data

Item number	1674969
Packing unit	100 pc
Minimum order quantity	1 pc
Sales key	BF65
Product key	AF7AIA
Catalog page	Page 507 (C-2-2019)
GTIN	4017918135669
Weight per piece (including packing)	0.732 g
Weight per piece (excluding packing)	0.7 g
Customs tariff number	85366990
Country of origin	DE

CK1,6-ED-0,37BU AU - Crimp contact



1674969

<https://www.phoenixcontact.com/us/products/1674969>

Technical data

Notes

General	for HC-M-12, HC-M-17, HC-M-03/04, HC-M-EMV, HC-D, HC-DD, HC-Q, and VC-D contact carriers
---------	--

Mounting

Assembly note	At voltages of < 5 V and currents < 5 mA, gold-plated contacts are recommended. The quality of a crimp connection is determined by DIN EN 60352-2.
---------------	---

Product properties

Product type	Crimp contact
Series	HC-M-12
	HC-M-EMV
	HC-D
	HC-DD
	VC-D
	HC-M-03/04
	HC-M-17
	HC-K
	HC-Q
	HC-COM
	HC-M-42
	HC-M-08-MBIT
Type	Individual female contact
Contact material type	turned

Connection data

Connection method	Crimp connection
Contact connection type	Socket
Connection technology	Crimp connection
Conductor cross section	0.14 mm ² ... 0.37 mm ²
Connection cross section AWG	26 ... 22
Stripping length of the individual wire	8 mm
Conductor cross section flexible	0.14 mm ² ... 0.37 mm ²

Material specifications

Contact material	Copper alloy
Contact surface material	gold-plated

Dimensions

Mechanical characteristics

CK1,6-ED-0,37BU AU - Crimp contact



1674969

<https://www.phoenixcontact.com/us/products/1674969>

Contact diameter	1.6 mm
------------------	--------

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	≥ 500

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

CK1,6-ED-0,37BU AU - Crimp contact


1674969

<https://www.phoenixcontact.com/us/products/1674969>



Drawings

Dimensional drawing



Dimensional drawing

CK1,6-ED-0,37BU AU - Crimp contact

1674969

<https://www.phoenixcontact.com/us/products/1674969>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1674969>



EAC

Approval ID: RU C-DE.AI30.B.01102

CK1,6-ED-0,37BU AU - Crimp contact



1674969

<https://www.phoenixcontact.com/us/products/1674969>

Classifications

ECLASS

ECLASS-13.0	27440204
-------------	----------

ETIM

ETIM 9.0	EC000796
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

CK1,6-ED-0,37BU AU - Crimp contact



1674969

<https://www.phoenixcontact.com/us/products/1674969>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f2a25a4c-e2f7-4643-8337-d61688f1db0b

EF3.0 Climate Change

CO2e kg	0.191 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com