




PRODUCT NUMBER SEE SHEET 2



spec ref *				dr Rainbow Zhan		2014/11/30		projection		MM		size A3		scale 3:2			
tolerance std				eng Rainbow Zhan		2014/12/26						ecn no -					
ASME Y14.5				chr LI-He He		2014/12/26											
				appr Pei-Ming Zheng		2014/12/26											
				product family				PwrBlade+				rel level Released					
surface		linear		0.X		±0.5				title 4HP + 16S RA STB HEADER		dwg no 10106124-4004002		rev A			
		0.XX		±0.25													
		0.XXX		±0.10													
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw				sheet 1 of 3	

A

B

C

D

A


B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.



dr	Rainbow Zhan	2014/11/30	projection	MM	size	A3	scale	3:2
eng	Rainbow Zhan	2014/12/26			ecn no	-		
chr	Li-He He	2014/12/26			rel level	Released		
appr	Pei-Ming Zheng	2014/12/26	product family		PwrBlade+			
FCi			title			4HP + 16S		rev
			RA STB HEADER			dwg no		A
10106124-4004002								
www.fci.com			cat. no.		Product - Customer Drw			sheet 3 of 3