




Technical Data

03.07.2023

Labels for control panel identification, thermal transfer
Helatag 1216, for rough surfaces

TAG08-15TC-1216-WH

Article Number 596-12152



Material: Type 1216, Polyethylene, white (1216)
Colour: White (WH)

Operating Temperature : -30 °C to +80 °C
Curing Temperature: from 0 °C

Self adhesive (Yes/No): Yes

Width (W): 8.00 mm
Height (H): 15.00 mm
Width of Liner (WL): 85.00 mm
Labels per Row: 10 pcs.

Thickness of Foil: 105 µm
Thickness of Adhesive (TA) nom.: 24 µm

Test Method
ISO 534

Adhesive: Acrylic
Initial tack: 17 N
Shear strength: 10 h

FINAT FTM 9
FINAT FTM 8

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



Technical Data

03.07.2023

Labels for control panel identification, thermal transfer
Helatag 1216, for rough surfaces

Print Method:	Thermal transfer print
Application Tool:	TT431, TT4030
Recommended Ribbon Type:	TT822OUT
Shelf Life:	Minimum 1 year upon receipt / maximal 2 years after production date.
Storage Temperature:	+15 °C to +25 °C
Storage conditions:	45% ±5% relative humidity., The storage in the original packaging is recommended., Please avoid warehousing under impacts such as high humidity, heat and coldness., Must be stored in a dark place.
Application Method:	The functionality and durability of the labels can be negatively affected if improperly processed or applied. All surfaces to be bonded must be clean, dry as well as free from dust and grease. Avoid touching the adhesive surface of the label as this could impair the application performance.

HF ✓

RoHS ✓

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved