


Customer Information Sheet


IF IN DOUBT - ASK	©	NOT TO SCALE	THIRD ANGLE PROJECTION	ALL DIMENSIONS IN mm









VIEW SHOWING CORNER OF
THE SHIELD CAN







ORDER CODE:

S01-XXXXXXX0

SIZE:
- DIM 'A' = LENGTH: 10-100mm
- DIM 'B' = WIDTH: 10-100mm
- DIM 'C' = HEIGHT: 3-10mm

FINISH:
- 0 = UNPLATED FINISH

NOTES:
1. DIM 'C', HEIGHT OF THE CAN IS FROM THE BOTTOM EDGE TO THE INSIDE OF THE TOP FACE.
2. BOTH DIM 'A' AND 'B' ARE FROM THE CENTRE OF THE MATERIAL THICKNESS.
3. CANS ARE PACKED IN MULTIPLES IN BOXES.
4. SHIELD CAN IS RECOMMENDED FOR USE WITH RFI SHIELD CLIPS: S1711-XXR AND S2711-XXR.
5. FOR LIST OF STOCKED SHIELD CAN SIZES, SEE S01-XXXXXXX0 CANS ON HARWIN.COM.
6. NON STANDARD SIZES AVAILABLE, PLEASE ENQUIRE FOR MORE DETAILS.

RTP	7	08.02.24	33642
NAME	ISS.	DATE	CN/CO
APPROVED:	R.PORTLOCK		
CHECKED:	A.YEOMANS		
DRAWN:	S.BENNETT		
ASSEMBLY DRG:			

HARWiN

www.harwin.com

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.20mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

MATERIAL:
NICKEL SILVER, HALF HARD NS106, TO BS1653 0.30mm THICK

TITLE:
EZi SHIELD CAN

DRAWING NUMBER:
S01-XXXXXXX0

SHT 2 OF 2

Downloaded from Arrow.com.