

MLCC with Dipped Radial Lead

[Product Top Page](#) | [Search by Part No.](#) | [Search by Characteristics](#) | [Cross Reference](#) | [Catalog](#) | [Tech Note](#) | [FAQ](#)

FK20C0G1H104JN006 ?




Applications Commercial Grade

Feature General General (Up to 50V)

Series FK

Status Production (Not Recommended for New Design)
Recommended Alternate Part No. : [FG26C0G1H104JNT06](#)



Images are for reference only and show exemplary products.

PDF file of this page

Contact

Documents

- [Catalog](#)
- [Specification](#)
- [RoHS Certificate](#)
- [SVHC/REACH Certificate](#)

Size	
Length(L)	5.50mm Max.
Width(W)	7.00mm Max.
Thickness(T)	4.00mm Max.
Lead Gap(F)	5.00mm +0.80,-0.20mm
Lead Diameter(d)	0.50mm +0.10,-0.03mm

Electrical Characteristics	
Capacitance	100nF ±5%
Rated Voltage	50VDC
Withstanding Voltage	150VDC
Temperature Characteristic ?	C0G(0±30ppm/°C)
Q (Min.)	1000
Insulation Resistance (Min.)	5000M?

Other	
Soldering Method	Flow Iron Soldering
Lead Length / Package Type	Taping
AEC-Q200	No
Package Quantity	1500pcs

Characteristic Graph (This is reference data, and does not guarantee the products characteristics.)

Impedance

no data available

Change settings

Capacitance

no data available

Change settings

DC Bias Characteristic

no data available

Change settings

Temperature Characteristic

no data available

Change settings

Products

» [Search by Part No.](#) » [Search by Characteristics](#) » [Distributor Inventory Check](#)

- | | |
|---|--|
| <ul style="list-style-type: none"> » Capacitors » Inductors (Coils) » EMC Components » RF / SAW Components and Modules » Voltage / Current / Temperature Protection Devices » Sensors and Sensor Systems » Ceramic Switching / Heating, Piezo Components and Buzzers » Transformers » Ferrites and Accessories | <ul style="list-style-type: none"> » Noise Suppressing / Magnet Sheets » Anechoic Chambers and Radio Wave Absorbers » Power Supplies » Magnets » Flash Storages » Wireless Charging » FA Systems » Transparent Conductive Film » Micro Modules (Substrates with Built-in ICs, Products Utilizing with SESUB) » Solar Cells |
|---|--|

Application Guides

- [Technical Support](#)
- [Tech Library](#)
- [Environment](#)
- [Contact](#)
- [News](#)
- [Home](#)

- [About TDK](#)
- [TDK Worldwide](#)