

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASE TO PRODUCTION	18DEC2014	NV	PS

REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.

POLARISATION SLOT

SECTION A-A

SCALE 3:1

SOLDER DETAIL
SCALE 10:1

EXAMPLE SOLDER JOINT

SEE DETAIL X

USER DIRECTION OF FEED

ACCORDING EIA-481/DIN IEC 286

POLARIZATION-SLOT
ON THIS SIDE.

DETAIL X
SCALE 1:1

NOTES:

- 1 TAPE FOR VACUUM P&P ONLY FOR DASH NUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 AND 3
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	BLACK
1	FEMALE CONTACT	TIN BRASS	TIN(3-5µ) OVER NICKEL
Item no.	Description	Material	Finish

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL	FINISH

SEE TABLE

SEE TABLE

DWN	25SEP2014
CHK	26SEP2014
APVD	26SEP2014
PRODUCT SPEC	108-32087
APPLICATION SPEC	114-13318
WEIGHT	-

Customer Drawing

TE

TE Connectivity

MICRO-MATCH VALUE LINE
FEMALE-ON-BOARD TOP-ENTRY,
SMD CONNECTOR WITH LATCHES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2823056	-

SCALE 5:1 SHEET 1 OF 3 REV A

RECOMMENDED PC-BOARD
PAD-LAYOUT TOP VIEW

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR


DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1



7-2823056-4

7-2823056-6

7-2823056-8

4 POSITIONS


6 POSITIONS

8 POSITIONS

2823056-4

2823056-6

2823056-8



8-2823056-0

8-2823056-2

8-2823056-4

8-2823056-6

8-2823056-8

10 POSITIONS

12 POSITIONS

14 POSITIONS

16 POSITIONS

18 POSITIONS


1-2823056-0

1-2823056-2

1-2823056-4

1-2823056-6

1-2823056-8



24mm
wide tape

24mm
wide tape

24mm
wide tape

44mm wide tape

44mm wide tape

44mm wide tape


44mm wide tape

44mm wide tape

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.
1 PLC ±.
2 PLC ±.
3 PLC ±.
4 PLC ±.
ANGLES ±.
FINISH -

MATERIAL

-

DWN 25SEP2014

Nagashree.V

CHK 26SEP2014

Prashanth.S

APVD 26SEP2014

Jayanth.K

PRODUCT SPEC

108-32087

APPLICATION SPEC

114-13318

WEIGHT

-

Customer Drawing



TE Connectivity

NAME
MICRO-MATCH VALUE LINE
FEMALE-ON-BOARD TOP-ENTRY,
SMD CONNECTOR WITH LATCHES.

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779


C-2823056

SCALE 4:1

SHEET 2 OF 3


REV A

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

MATERIAL -

FINISH -

DWN Nagashree.V 25SEP2015

CHK Prashanth.S 26SEP2014

APVD JAYANTH 26SEP2014

PRODUCT SPEC 108-32087

APPLICATION SPEC 114-13318

WEIGHT -

Customer Drawing

 TE Connectivity

NAME MICRO-MATCH VALUE LINE FEMALE-ON-BOARD TOP-ENTRY, SMD CONNECTOR WITH LATCHES.

SIZE A3

CAGE CODE 00779

DRAWING NO C-2823056

RESTRICTED TO -

SCALE 4:1

SHEET 3 OF 3

REV A