


Product Status	Obsolete
	Recommended Alternate Part No. : MMZ1608D800BTA00 (Interchangeability is not guaranteed.)
	Discontinue Issue Date : Nov.22, 2022
	Last Purchase Order Date : Jun.30, 2024
	Last Shipment Date : Dec.30, 2024
Applications	Commercial Grade
Feature	High SpeedHigh speed signal line
Series	MMZ
Brand	TDK
Environmental Compliance	<div><div>RoHS</div><div>REACH</div><div>Halogen Free</div><div>Lead Free</div></div>





Size	
Length(L)	2.00mm ±0.20mm
Width(W)	1.25mm ±0.20mm
Thickness(T)	0.85mm ±0.20mm
Recommended Land Pattern (A)	0.80mm Nom.
Recommended Land Pattern (B)	1.00mm Nom.
Recommended Land Pattern (C)	1.20mm Nom.

Electrical Characteristics	
Impedance at 100MHz	80Ω ±25%
Rated Current	500mA
DC Resistance (Max.)	300mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow
	Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	4000pcs
Weight	0.008g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



Associated Images

