

Regulated Converters

- 4:1 Wide Input Voltage Range
- 1.6kVDC Isolation
- UL Certified
- Efficiency up to 84%
- Fixed Operating Frequency
- Six-Sided Continuous Shield



RP10-EW

10 Watt

2" x 1"

Single & Dual Output



Description

The RP10-EW series wide input range DC/DC converters are certified to UL 60950-1 and cUL 60950-1. This makes them ideal for all telecom and industrial applications where approved safety standards are required. The industry standard 2" x 1" package meets military standards for thermal shock and vibration tolerance and is available with an optional remote on/off control pin.

Selection Guide

Part Number	Input Voltage Range [VDC]	Output Voltage [VDC]	Output Current [mA]	Input ⁽¹⁾ Current [mA]	Efficiency ⁽¹⁾ typ. [%]	Max. Capacitive Load ⁽²⁾ [μF]
RP10-243.3SEW ^(3,4)	9-36	3.3	2500	441	78	6800
RP10-2405SEW ^(3,4)	9-36	5	2000	521	80	4700
RP10-2412SEW ^(3,4)	9-36	12	830	494	84	690
RP10-2415SEW ^(3,4)	9-36	15	670	517	81	470
RP10-483.3SEW ^(3,4)	18-75	3.3	2500	226	76	6800
RP10-4805SEW ^(3,4)	18-75	5	2000	322	81	4700
RP10-4812SEW ^(3,4)	18-75	12	830	247	84	690
RP10-4815SEW ^(3,4)	18-75	15	670	249	84	470
RP10-2405DEW ^(3,4)	9-36	±5	±1000	508	82	±680
RP10-2412DEW ^(3,4)	9-36	±12	±416	520	80	±330
RP10-2415DEW ^(3,4)	9-36	±15	±333	520	80	±110
RP10-4805DEW ^(3,4)	18-75	±5	±1000	254	82	±680
RP10-4812DEW ^(3,4)	18-75	±12	±416	267	78	±330
RP10-4815DEW ^(3,4)	18-75	±15	±333	257	81	±110




Notes:

Note1: Maximum value at nominal input voltage and full load.

Note2: Test by minimum Vin and constant resistor load.

Model Numbering



Ordering Examples:

RP10-1205SEW/P = 12V Input, 5V Output, Positive Logic CTRL pin fitted

RP10-4805DEW-HC = 48V Input, 5V Output, No CTRL pin, Heatsink fitted

Notes:

Note3: add suffix "P" for CTRL function with Positive Logic (1=ON, 0=OFF)

add suffix "N" for CTRL function with Negative Logic (0=ON, 1=OFF)

Note4: add suffix -HC for premounted Heat-sink and clips



UL[®]
C US
E196683

UL60950-1 Certified

Specifications measured at $T_a = 25^\circ\text{C}$, nominal input voltage, full load otherwise noted

BASIC CHARACTERISTICS

Parameter	Condition	Min.	Typ.	Max.
Input Voltage Range	nom. $V_{in} = 24\text{V}$ nom. $V_{in} = 48\text{V}$	9VDC 18VDC	24VDC 48VDC	36VDC 75VDC
Under Voltage Lockout (UVLO)		none		
Input Filter		Pi-Type		
Input Reflected Ripple Current ⁽⁵⁾	nominal V_{in} and full load		30mA _{p-p}	
Input Surge Voltage	$V_{in} = 24\text{V}$, 100ms max. $V_{in} = 48\text{V}$, 100 ms max.			50VDC 100VDC
Start-up time	nominal V_{in} and constant resistor load		20ms	
Operating Frequency Range		270kHz	300kHz	330kHz
Minimum Load ⁽⁶⁾	of full load	10%		
Ripple and Noise	20MHz bandwidth	Single Dual	50mV _{p-p} 75mV _{p-p}	
Remote ON/OFF ⁽⁷⁾	Positive Logic	DC-DC ON DC-DC OFF	Open or $3.5\text{V} < V_r < 12\text{V}$ Short or $0\text{V} < V_r < 1.2\text{V}$	
	Negative Logic	DC-DC ON DC-DC OFF	Short or $0\text{V} < V_r < 1.2\text{V}$ Open or $3.5\text{V} < V_r < 12\text{V}$	
Input current of Remote pin (CTRL)		DC-DC OFF	20mA	
		DC-DC ON	-0.5mA	1.0mA

Notes:

Note5: Simulated source impedance of 12 μH . 12 μH inductor in series with + V_{in} .

Note6: The RP10 (W) series required a minimum 10% loading on the output to maintain specified regulation.


Operation under no-load condition will not damage these devices, however they may not meet all listed specification.

Note7: The ON/OFF control function can be positive or negative logic. The pin voltage is referenced to - V_{in} pin.


If no suffix is specified, the control pin will be omitted.

RP10-2405SEW

Efficiency vs. Output Current



Efficiency vs. Input Voltage




continued on next page


Specifications measured at Ta = 25°C, nominal input voltage, full load otherwise noted

RP10-4805SEW

Efficiency vs. Output Current



Efficiency vs. Input Voltage



REGULATIONS

Parameter	Condition		Value
Output Voltage Accuracy			±1%
Load Voltage Regulation	0% to 100% load	Single	±0.5%
		Dual	±1.0%
Line Voltage Regulation	low line to high line, full load		±0.2%
Cross Regulation	asymmetrical 25%<>100% load		±5%
Transient Response recovery time	25% load step change		250µs

PROTECTIONS

Parameter	Condition		Value
Short Circuit Protection (SCP)			Continuous, automatic recovery
Over Voltage Protection (OVP)	Zener Diode Clamp	5Vout	6.2VDC
		12Vout	15VDC
		15Vout	18VDC
Over Load Protection (OLP)	%of lout rated		150% typ.
Isolation Voltage	I/P to O/P		1.6kVDC/1 minute
	I/P (O/P) to case		1.6kVDC/1 minute
Isolation Resistance	500VDC		1GΩ min.
Isolation Capacitance			300pF max.



Notes:

Note8: This power module is not internally fused. An input line fuse must always be used.

Specifications measured at Ta = 25°C, nominal input voltage, full load otherwise noted

ENVIRONMENTAL		
Parameter	Condition	Value
Operating Temperature Range	without derating	-40°C to +78°C
	with derating	-40°C to +94°C
Maximum Case Temperature		+105°C
Temperature Coefficient		±0.02%/°C max.
Thermal Impedance ⁽⁹⁾	Natural convection (20LFM)	12°C/Watt
	Natural convection (20LFM) with heatsink	10°C/Watt
Operating Humidity	non-condensing	5% - 95% RH
Thermal Shock		MIL-STD-810F
Vibration		MIL-STD-810F
MTBF	MIL-HDBK-217F, Full Load	3342 x 10 ³ hours
	Bellco TR-NWT-000332 ⁽¹⁰⁾	1976 x 10 ³ hours

Derating Graph⁽¹¹⁾



Notes:

- Note9: Heatsink is optional and P/N 7G-0020C. Powerline DC/DC Converters can be ordered with pre-mounted heatsinks including antivibration fixing clips (add suffix -HC). See application notes for further details.
- Note10: BELLCORE TR-NWT-000332. Case I: 50% Stress, Temperature at 40°C. (Ground fixed and controlled environment).
- Note11: Derating graphs are valid only for the shown part numbers. If you need detailed derating-information about a part-number not shown here please contact our technical support service at techsupportAT@recom-power.com

SAFETY AND CERTIFICATIONS		
Certificate Type (Safety)	Report / File Number	Standard
UL General Safety	E196683	UL60950-1 1st Ed.: 2003 C22.2 No. 60950 1st. Ed.: 2003
EMC Compliance	Condition	Standard / Criterion
EMI Standard ⁽¹²⁾	with external filter	EN55022, Class A or B
ESD	Air ±8kV and Contact ± 6kV	EN61000-4-2, Criteria B
Radiated Immunity	10 V/m	EN61000-4-3, Criteria A
Fast Transient ⁽¹³⁾	±2kV	EN61000-4-4, Criteria B
Surge ⁽¹³⁾	±2kV	EN61000-4-5, Criteria B
Conducted Immunity	10 Vr.m.s	EN61000-4-6, Criteria A

continued on next page



Specifications measured at $T_a = 25^\circ\text{C}$, nominal input voltage, full load otherwise noted

Notes:

Note12: The standard modules meet EMI Class A or Class B with external components, see filter suggestions below.



Note13: An external input filter capacitor is required if the module has to meet EN61000-4-4, EN61000-4-5. The filter capacitor Recom suggests: Nippon chemi-con KY series, 220 μF /100V

EMC Filtering Class A



MODEL	C1	C2	L1
RP10-24xxS_DEW	1 μF /50V 1210 MLCC	1000pF/2kV 1808 MLCC	1000pF/2kV 1808 MLCC
RP10-48xxS_DEW	1.5 μF /100V 1812 MLCC	1000pF/2kV 1808 MLCC	1000pF/2kV 1808 MLCC

EMC Filtering Class B








MODEL	C1	C2	C3/C4	L1
RP10-24xxS_DEW	2.2 μF /50V 1812 MLCC	N/A	1000pF/2kV 1808 MLCC	CMC: 325 μH ref: WE 744290321 ref.: CMC-06
RP10-48xxS_DEW	2.2 μF /50V 1812 MLCC	2.2 μF /100V 1812 MLCC	1000pF/2kV 1808 MLCC	CMC: 325 μH ref: WE 744290321 ref.: CMC-06

Specifications measured at Ta = 25°C, nominal input voltage, full load otherwise noted

DIMENSIONS and PHYSICAL CHARACTERISTICS

Parameter	Type	Value
Material	Case	Nickel coated copper
	Base	Non-conductive black plastic
	Potting	Epoxy (UL94-V0)
Package Dimensions (LxWxH)	without Heat-sink	50.8 x 25.4 x 10.2mm
	with Heat-sink	56.8 x 25.4 x 16.8mm
Package Weight	without Heat-sink	27g
	with Heat-sink	37.89g

Dimension Drawing (mm)






Pin Connections

Pin #	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	+Vout	+Vout
4	No Pin	Com
5	-Vout	-Vout
6*	CTRL*	CTRL*

*optional see Note7
Pin Pitch Tolerance $\pm 0.25\text{mm}$
Pin Dimension Tolerance $\pm 0.1\text{mm}$
XX.X $\pm 0.5\text{mm}$
XX.XX $\pm 0.25\text{mm}$

Dimension Drawing (mm) with Heat-sink



Specifications measured at Ta = 25°C, nominal input voltage, full load otherwise noted

PACKAGING INFORMATION		
Parameter	Type	Value
Packaging Quantity	without Heat-sink	9pcs.
	with Heat-sink	20pcs.
Storage Temperature Range		-55°C to +125°C
Storage Humidity		5% - 95% RH

The product information and specifications are subject to change without prior notice. RECOM products are not authorized for use in safety-critical applications (such as life support) without RECOM's explicit written consent. A safety-critical application is defined as an application where a failure of a RECOM product may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The buyer shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.