


ASSY NO.	PROTECTIVE CAP	CHAIN	WASHER	A THREAD CLASS 2 A	B DIA +.010-.000	C APPROX	L MAX	COMMENT NUMBER	RELEASE NUMBER	WEIGHT-LB
10-37399-10	10-35886-10	10-35890-2	10-35878-101	.6250-24NEF	.516	3.000	1.250	22021-216	25808-48	
10-37399-12	10-35886-12	10-35890-4	10-35878-121	.7500-20UNEF	.641	3.500	1.438	22021-217	25808-48	
10-37399-14	10-35886-14	10-35890-4	10-35878-141	.8750-20UNEF	.766			22021-218	25808-48	
10-37399-16	10-35886-16	10-35890-4	10-35878-161	1.0000-20UNEF	.891			22021-219	25808-48	
10-37399-40	10-35886-40	10-35891-8	10-35878-401	2.5000-16UN	2.328	5.000			37524-104	.1670
10-37399-44	10-35886-44	10-35891-8	10-35878-441	2.7500-16UN	2.641					
10-37399-48	10-35886-48	10-35891-8	10-35878-481	3.0000-16UN	2.891					
10-37399-18	10-35886-18	10-35891-2	10-35878-181	1.1250-18NEF	1.016	3.500		21996-98	24708-135	.0521
10-37399-20	10-35886-20	10-35891-4	10-35878-201	1.2500-18NEF	1.141	4.000		21996-99	24708-135	
10-37399-22	10-35886-22	10-35891-4	10-35878-221	1.3750-18NEF	1.266			22021-220	25808-48	.0640
10-37399-24	10-35886-24	10-35891-6	10-35878-241	1.5000-18NEF	1.391	4.500		21996-100	24708-135	
10-37399-28	10-35886-28	10-35891-6	10-35878-281	1.7500-18NS	1.641			21996-101	24708-135	
10-37399-32	10-35886-32	10-35891-8	10-35878-321	2.000-18NS	1.891	5.000		21996-102	24708-135	
10-37399-36	10-35886-36	10-35891-8	10-35878-361	2.2500-16UN	2.078			21996-103	24708-135	.1370

REL	24708-135	WAS	DATE	D'MAN	APPD.
1	CNR	ADDED -28 4-36	9-6-49	WPH	
2	P1007-4	SPIN OVER ADDED RIVET 10-35894-1 -10, -12, -14, -16 +22 DATA	11-22-49	WPH	
3	28460-12	ADD: .062 (2), 10-37399-1, STAMPING NOTE.	4-14-53	C.M.	
4	30457-11	REV. STAMPING NOTE: ADD: 9-2811 (PRO. SPEC.), NOTE 2	1-27-55		
5	31525-254	ADD -40, -44, -48	4-30-56	E. Michel	
6	33525-298	RELOCATE STAMPING SIZE 18 THRU 48	9-17-58	MAXLEY	
7	35220-5	SIZES 18, 20, 28, 30 (NOTE 2); REM: .062 (2 PLACES); VIEW FOR SIZES 18-48; ADDED: .031 +.016 - .000; REVISED LOCAL NOTE; RELOC STAMPING	4-27-59		
8	37524-104	REL -40 & DATA	11-9-60	HISCOT	
9	39264-21	REM RIVET 8# RIVET COLS; ADD. COLS A THREAD CLASS 2A, B +.010-.000 DIA, C APPROX, L MAX & DATA, NOTE 1; REV TITLE; RENUM NOTES	2-27-62	D. KEMAN	
10	40180-3	ADD VIEW F	8-20-62	Darlin	
11	40024-11	10-35892 (RIVET)	8-28-62	Darlin	
A1	44937-11	(MFG); 10-35894 (RIVET)	5-7-65	NELSON	



VIEW F
PERMISSIBLE ALTERNATE STAMPING
SIZES - 18 THRU - 48

3. BENDIX TRADEMARK IS CAST IN ON SIZES 18 THRU 36 AND IS PERMISSIBLE IN PLACE OF BENDIX.

2. CHAIN MUST MOVE FREELY ON PROTECTIVE CAP AFTER ASSEMBLY.

1. CAP
MATERIAL: ALUMINUM ALLOY
FINISH: BRIGHT CADMIUM PLATE
CHAIN
MATERIAL: BRASS
FINISH: NICKEL PLATE

NOTES: REF SYMBOL

USE OF THIS DOCUMENT IS UNLIMITED. DOCUMENTS REFERENCED HEREON CONTAIN LIMITED RIGHTS DATA.

MATERIAL SPEC.	PROCESS SPEC. 9-2811	SCINTILLA MAGNETO DIVISION BENDIX AVIATION CORPORATION SIDNEY, N. Y., U. S. A.						TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/32 DECIMALS ± .010 ANGLES ± 3° CONCENTRICITY .015 FIR. BREAK SHARP EDGES .010-0.00 SQUARENESS .010 PER INCH OF LENGTH MACHINED SURFACES MUST BE FLAT AND PARALLEL WITHIN THE TOLERANCE OF THE APPLICABLE DIMENSION AND SMOOTH WITHIN 200 MICRO-INCHES RMS.			
HEAT TREAT. SPEC.	FINISH SPEC.	CAP PROTECTIVE, PLUG, ASSEMBLY OF						NEXT ASSEMBLY			
		NAME						WEIGHT-LBS. SEE COL			
		D'MAN CHECKER MAT. STDS CH. D'MAN APPROVED SCALE						SUPERSEDES AND IS NOT INTERCHANGEABLE			
		B.F. 8/3/49 8-31-49 9-2-49						10-37399			
		TOOL ACC. CON. REC.						REF			

DWG SIZE C

TAB. CODE 77620