Field Stop Trench IGBT

50 A, 650 V

AFGHL50T65SQ

Using the novel field stop 4th generation high speed IGBT technology. AFGHL50T65SQ which is AEC Q101 qualified offers the optimum performance for both hard and soft switching topology in automotive application. It is a stand−alone IGBT.


Features


- AEC−Q101 Qualified
- Maximum Junction Temperature: T_J = 175°C
- Positive Temperature Co−efficient for Easy Parallel Operating
- High Current Capability
- Low Saturation Voltage: $V_{CE(Sat)}$ = 1.6 V (Typ.) @ I_C = 50 A
- 100% of the Parts are Tested for I_{LM} (Note 2)
- Fast Switching
- Tight Parameter Distribution
- RoHS Compliant

Typical Applications

- Automotive HEV−EV Onboard Chargers
- Automotive HEV−EV DC−DC Converters
- Totem Pole Bridgeless PFC
- PTC


50 A, 650 V
V_{CESat} = 1.6 V





TO−247−3L
CASE 340CX

MARKING DIAGRAM



&Z = Assembly Plant Code
&3 = 3−Digit Date Code
&K = 2−Digit Lot Traceability Code
AFGHL50T65SQ = Specific Device Code

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector−to−Emitter Voltage	V_{CES}	650	V
Gate−to−Emitter Voltage Transient Gate−to−Emitter Voltage	V_{GES}	±20 ±30	V
Collector Current (Note 1) @ T_C = 25°C @ T_C = 100°C	I_C	80 50	A
Pulsed Collector Current (Note 2)	I_{LM}	200	A
Pulsed Collector Current (Note 3)	I_{CM}	200	A
Maximum Power Dissipation @ T_C = 25°C @ T_C = 100°C	P_D	268 134	W
Operating Junction / Storage Temperature Range	T_J, T_{STG}	−55 to +175	°C
Maximum Lead Temp. for Soldering Purposes, 1/8″ from case for 5 seconds	T_L	300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Value limit by bond wire
2. V_{CC} = 400 V, V_{GE} = 15 V, I_C = 200 A, R_G = 15 Ω, Inductive Load
3. Repetitive Rating: pulse width limited by max. Junction temperature

ORDERING INFORMATION

Device	Package	Shipping
AFGHL50T65SQ	TO−247−3L	30 Units / Rail

© Semiconductor Components Industries, LLC, 2019

Downloaded from Arrow.com.

THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal resistance junction−to−case, for IGBT	$R_{\theta JC}$	0.56	°C/W
Thermal resistance junction−to−ambient	$R_{\theta JA}$	40	°C/W

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Collector−emitter breakdown voltage, gate−emitter short−circuited	V_{GE} = 0 V, I_C = 1 mA	BV_{CES}	650	–	–	V
Temperature Coefficient of Breakdown Voltage	V_{GE} = 0 V, I_C = 1 mA	$\frac{\Delta BV_{CES}}{\Delta T_J}$	–	0.6	–	V/°C
Collector−emitter cut−off current, gate−emitter short−circuited	V_{GE} = 0 V, V_{CE} = 650 V	I_{CES}	–	–	250	μA
Gate leakage current, collector−emitter short−circuited	V_{GE} = 20 V, V_{CE} = 0 V	I_{GES}	–	–	±400	nA
ON CHARACTERISTICS						
Gate−emitter threshold voltage	V_{GE} = V_{CE}, I_C = 50 mA	$V_{GE(th)}$	3.4	4.9	6.4	V
Collector−emitter saturation voltage	V_{GE} = 15 V, I_C = 50 A V_{GE} = 15 V, I_C = 50 A, T_J = 175°C	$V_{CE(sat)}$	– –	1.6 1.95	2.1 –	V
DYNAMIC CHARACTERISTICS						
Input capacitance	V_{CE} = 30 V, V_{GE} = 0 V, f = 1 MHz	C_{ies}	–	3209	–	pF
Output capacitance		C_{oes}	–	42	–	
Reverse transfer capacitance		C_{res}	–	12	–	
Gate charge total	V_{CE} = 400 V, I_C = 50 A, V_{GE} = 15 V	Q_g	–	99	–	nC
Gate−to−emitter charge		Q_{ge}	–	17	–	
Gate−to−collector charge		Q_{gc}	–	23	–	
SWITCHING CHARACTERISTICS, INDUCTIVE LOAD						
Turn−on delay time	T_C = 25°C, V_{CC} = 400 V, I_C = 25 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, FWD: AFGHL50T65SQD	$t_{d(on)}$	–	19	–	ns
Rise time		t_r	–	11	–	
Turn−off delay time		$t_{d(off)}$	–	87	–	
Fall time		t_f	–	5	–	
Turn−on switching loss		E_{on}	–	0.35	–	mJ
Turn−off switching loss		E_{off}	–	0.12	–	
Total switching loss		E_{ts}	–	0.47	–	
Turn−on delay time	T_C = 25°C, V_{CC} = 400 V, I_C = 50 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, FWD: AFGHL50T65SQD	$t_{d(on)}$	–	20	–	ns
Rise time		t_r	–	28	–	
Turn−off delay time		$t_{d(off)}$	–	81	–	
Fall time		t_f	–	36	–	
Turn−on switching loss		E_{on}	–	0.95	–	mJ
Turn−off switching loss		E_{off}	–	0.46	–	
Total switching loss		E_{ts}	–	1.41	–	

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted) (Continued)

Parameter	Test Conditions	Symbol	Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS, INDUCTIVE LOAD						
Turn−on delay time	T_J = 175°C, V_{CC} = 400 V, I_C = 25 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, FWD: AFGHL50T65SQD	$t_{d(on)}$	−	18	−	ns
Rise time		t_r	−	14	−	
Turn−off delay time		$t_{d(off)}$	−	99	−	
Fall time		t_f	−	7	−	
Turn−on switching loss		E_{on}	−	0.66	−	mJ
Turn−off switching loss		E_{off}	−	0.3	−	
Total switching loss		E_{ts}	−	0.96	−	
Turn−on delay time	T_J = 175°C, V_{CC} = 400 V, I_C = 50 A, R_G = 4.7 Ω, V_{GE} = 15 V, Inductive Load, FWD: AFGHL50T65SQD	$t_{d(on)}$	−	20	−	ns
Rise time		t_r	−	29	−	
Turn−off delay time		$t_{d(off)}$	−	88	−	
Fall time		t_f	−	46	−	
Turn−on switching loss		E_{on}	−	1.42	−	mJ
Turn−off switching loss		E_{off}	−	0.65	−	
Total switching loss		E_{ts}	−	2.07	−	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. Typical Output Characteristics




Figure 2. Typical Output Characteristics




Figure 3. Typical Saturation Voltage




Figure 4. Saturation Voltage vs. Case Temperature




Figure 5. Saturation Voltage vs. V_{GE}




Figure 6. Saturation Voltage vs. V_{GE}

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge




Figure 9. Turn−On Characteristics vs. Gate Resistance




Figure 10. Turn−Off Characteristics vs. Gate Resistance




Figure 11. Turn−On Characteristics vs. Collector Current




Figure 12. Turn−Off Characteristics vs. Collector Current

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 13. Switching Loss vs. Gate Resistance




Figure 14. Switching Loss vs. Collector Current




Figure 15. SOA Characteristics





Figure 16. transient Thermal Impedance of IGBT


Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TO−247−3LD
CASE 340CX
ISSUE A

DATE 06 JUL 2020





NOTES: UNLESS OTHERWISE SPECIFIED.

A. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS.
B. ALL DIMENSIONS ARE IN MILLIMETERS.
C. DRAWING CONFORMS TO ASME Y14.5 - 2009.
D. DIMENSION A1 TO BE MEASURED IN THE REGION DEFINED BY L1.
E. LEAD FINISH IS UNCONTROLLED IN THE REGION DEFINED BY L1.

DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.58	4.70	4.82
A1	2.20	2.40	2.60
A2	1.40	1.50	1.60
D	20.32	20.57	20.82
E	15.37	15.62	15.87
E2	4.96	5.08	5.20
e	~	5.56	~
L	19.75	20.00	20.25
L1	3.69	3.81	3.93
ØP	3.51	3.58	3.65
Q	5.34	5.46	5.58
S	5.34	5.46	5.58
b	1.17	1.26	1.35
b2	1.53	1.65	1.77
b4	2.42	2.54	2.66
c	0.51	0.61	0.71
D1	13.08	~	~
D2	0.51	0.93	1.35
E1	12.81	~	~
ØP1	6.60	6.80	7.00

GENERIC MARKING DIAGRAM*



XXXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “ ▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON93302G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	**TO−247−3LD**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2018

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.