

6

5

4

3

2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/10	

APPROVED: _____

DATE: _____ TITLE: _____

D


.024 [0.60]




RECOMMENDED PCB LAYOUT

C

.183 [4.65]



B



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Beige, 4685C follow Pantone color.

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 125 V AC,DC.

Current rating: 2A AC,DC

Contact resistance: 20 mohms max. initial

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 02 thru 15
A = .079 [2.00] x No. of Spaces
B = .079 [2.00] x No. of Spaces + .157 [4.00]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

.079 [2.00] WAFER, PCB TYPE, RIGHT ANGLE

TIN PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				ADAM TECH				
INCHES				909 Railway Avenue, Union, NJ 07083				
HOLES				Phone: 908-687-5000 Fax: 908-687-5710				
.X	± .10	ØX	± .10	TITLE .079 [2.00] WAFER, PCB TYPE, RIGHT ANGLE				
.XX	± .020	ØXX	± .015					
.XXX	± .015	ØXXX	± .010					
APPROVALS		DATE		SIZE PART NO. 2SH-F-XX-TR				
DRAWN	AY	11/23/10						
CHECKED	AH	11/23/10						
APPROVED				REF:	S00099T	SCALE: NTS	SHEET 1 OF 1	REV: -

A

B

C

D

A