

## Data Sheet | Item Number: 713-1437/107-000



THT male header, 2-row; 0.8 x 0.8 mm solder pin; angled; 100% protected against mismatching; Threaded flange; Pin spacing 3.5 mm; 34-pole; black

<https://www.wago.com/713-1437/107-000>




Color: ■ black

Similar to illustration



Dimensions in mm

$L = [(pole\ no./2) - 1] \times pin\ spacing + 13.6\ mm$



Male connector, 713 Series, black

Enjoy error-free electrical installations with this male connector (item number 713-1437/107-000). Dimensions: (69.6 x 17.1 x 13.5) mm (width x height x depth).

The contact surface is coated with tin. The pcb connector is designed for THT soldering.

## Notes

## Safety Information

The MCS – MULTI CONNECTION SYSTEM includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

## Variants:

Other pole numbers  
Other solder pin lengths  
Gold-plated or partially gold-plated contact surfaces  
Other versions (or variants) can be requested from WAGO Sales or configured at <https://configurator.wago.com/>.

## Electrical data

Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	80 V	160 V	250 V
Rated impulse withstand voltage	2.5 kV	2.5 kV	2.5 kV
Rated current	10 A	10 A	10 A

Approvals per	UL 1059		
Use group	B	C	D
Rated voltage	150 V	50 V	-
Rated current	10 A	10 A	-

Approvals per	CSA		
Use group	B	C	D
Rated voltage	150 V	-	-
Rated current	12 A	-	-

## Connection Data

Total number of potentials	34
Number of connection types	1
Number of levels	2

## Connection 1

Pole number	34
-------------	----

## Physical data

Pin spacing	3.5 mm / 0.138 inches
Width	69.6 mm / 2.74 inches
Height	17.1 mm / 0.673 inches
Height from the surface	13.3 mm / 0.524 inches
Depth	13.5 mm / 0.531 inches
Solder pin length	3.8 mm
Solder pin dimensions	0.8 x 0.8 mm
Drilled hole diameter with tolerance	1.2 (+0.1) mm

## Mechanical data

Variable coding	Yes
Anti-rotation protection	Yes

### Plug-in connection

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mismatching protection	Yes
Mating direction to the PCB	0°
Locking of plug-in connection	Threaded flange

### PCB contact

PCB contact	THT
Solder pin arrangement	over the entire male connector (in-line)
Number of solder pins per potential	1

### Material data

Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	black
Material group	I
Insulation material (main housing)	Polyphthalamide (PPA GF)
Flammability class per UL94	V0
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact Plating	Tin
Fire load	0.183 MJ
Weight	9.9 g

### Environmental requirements

Limit temperature range	-60 ... +100 °C
Processing temperature	-35 ... +60 °C

### Commercial data

Product Group	3 (Multi Conn. System)
PU (SPU)	10 pcs
Packaging type	Box
Country of origin	PL
GTIN	4045454809249
Customs tariff number	85366930000

### Product Classification

UNSPSC	39121409
eCl@ss 10.0	27-44-04-02
eCl@ss 9.0	27-44-04-02
ETIM 9.0	EC002637
ETIM 10.0	EC002637
ECCN	NO US CLASSIFICATION

**Environmental Product Compliance**

RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c)
SCIP notification number (Austria)	8bb244ad-e269-4180-8b2d-80229c09c4e5
SCIP notification number (Belgium)	fcdb99f5-ef28-4827-a611-88e1550227b6
SCIP notification number (Bulgaria)	76d9f24b-5e88-4e16-89eb-11715f473898
SCIP notification number (Czech Republic)	916097e0-6e60-456c-b82d-db437922e365
SCIP notification number (Denmark)	2c2e4673-dc35-4d2f-9a3b-989fe0c00a06
SCIP notification number (Finland)	7c8b5de6-c8bd-415e-a301-9793327cd3e3
SCIP notification number (France)	f9790d6b-d0aa-4247-a043-efd8b660a7e0
SCIP notification number (Germany)	ba037fcb-657a-4e6e-a4b5-1ff627152af4
SCIP notification number (Hungary)	f5805528-f691-482e-8ce1-ca10f1d1e000
SCIP notification number (Italy)	6aa34f57-e848-4291-acdb-25ef57663a90
SCIP notification number (Netherlands)	9019b81c-6cb1-4d76-9c90-40ff13891762
SCIP notification number (Poland)	a03a8732-3f49-480e-acc3-0072777e96d6
SCIP notification number (Romania)	dd0a8849-0bfc-464a-a221-656c4c1256e1
SCIP notification number (Sweden)	5cd3e6dc-b2d1-4337-b02b-f3ee925aee9f

**Approvals / Certificates**

**General approvals**



Approval	Standard	Certificate Name
CB DEKRA Certification B.V.	IEC 61984	NL-102427
CSA CSA Group	C22.2	2315087
KEMA/KEUR DEKRA Certification B.V.	EN 61984	71-133740

**Downloads**

**Environmental Product Compliance**

Compliance Search
Environmental Product Compliance 713-1437/107-000

**Documentation**

Additional Information			
Technical Section	03.04.2019	pdf 2027.26 KB	

CAD/CAE-Data

CAD data

2D/3D Models  
713-1437/107-000



CAE data

ZUKEN Portal  
713-1437/107-000



PCB Design

Symbol and Footprint  
via SamacSys  
713-1437/107-000



Symbol and Footprint  
via Ultra Librarian  
713-1437/107-000



1 Compatible Products

1.1 System counterpart

1.1.1 Female connector/socket



**Item No.: 713-1117/107-000**

1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 34-pole; 100% protected against mismatching; Screw flange; black



**Item No.: 713-1117/107-047**

1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 34-pole; 100% protected against mismatching; Screw flange; direct marking; black



**Item No.: 713-1117/107-9037**

1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 34-pole; 100% protected against mismatching; Screw flange; direct marking; black



**Item No.: 713-1117/107-047/035-000**

1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 34-pole; 100% protected against mismatching; Screw flange; Strain relief plate; direct marking; black



**Item No.: 713-1117/107-9037/035-000**

1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm<sup>2</sup>; Pin spacing 3.5 mm; 34-pole; 100% protected against mismatching; Screw flange; Strain relief plate; direct marking; black

1.2 Optional Accessories

1.2.1 Coding

1.2.1.1 Coding




**Item No.: 714-101**

Coding key; orange

Installation Notes

Coding



Coding a male header by inserting a coding pin.

Subject to changes. Please also observe the further product documentation!

---

Current addresses can be found at: [www.wago.com](http://www.wago.com)