

VZS Series

Features

- $5\phi \sim 10\phi$, 105°C, 2,000 hours assured
- Low impedance 30 ~ 50% less than VZH series
- Large capacitance with ultra low impedance capacitors
- Designed for surface mounting on high density PC board
- RoHS compliant
- AEC-Q200 compliant


Marking color: Black



Specifications

Items	Performance																							
Category Temperature Range	-55℃ ~ +105℃																							
Capacitance Tolerance	± 20% (at 120 Hz, 20℃)																							
Leakage Current (at 20℃)	I = 0.01CV or 3 (μA) whichever is greater (after 2 minutes) Where, C = rated capacitance in μF, V = rated DC working voltage in V																							
Tanδ (at 120 Hz, 20℃)	<table><tr><td>Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td>Tanδ (max.)</td><td>0.30</td><td>0.26</td><td>0.22</td><td>0.16</td><td>0.13</td><td>0.10</td></tr></table> When the capacitance exceeds 1,000μF, 0.02 shall be added every 1,000μF increase.	Rated Voltage	6.3	10	16	25	35	50	Tanδ (max.)	0.30	0.26	0.22	0.16	0.13	0.10									
Rated Voltage	6.3	10	16	25	35	50																		
Tanδ (max.)	0.30	0.26	0.22	0.16	0.13	0.10																		
Low Temperature Characteristics (at 120 Hz)	Impedance ratio shall not exceed the values given in the table below. <table><tr><td colspan="2">Rated Voltage</td><td>6.3</td><td>10</td><td>16</td><td>25</td><td>35</td><td>50</td></tr><tr><td rowspan="2">Impedance Ratio</td><td>Z(-25℃) / Z(+20℃)</td><td>4</td><td>3</td><td>2</td><td>2</td><td>2</td><td>2</td></tr><tr><td>Z(-55℃) / Z(+20℃)</td><td>8</td><td>5</td><td>4</td><td>3</td><td>3</td><td>3</td></tr></table>	Rated Voltage		6.3	10	16	25	35	50	Impedance Ratio	Z(-25℃) / Z(+20℃)	4	3	2	2	2	2	Z(-55℃) / Z(+20℃)	8	5	4	3	3	3
Rated Voltage		6.3	10	16	25	35	50																	
Impedance Ratio	Z(-25℃) / Z(+20℃)	4	3	2	2	2	2																	
	Z(-55℃) / Z(+20℃)	8	5	4	3	3	3																	
Endurance	<table><tr><td>Test Time</td><td>2,000 Hrs</td></tr><tr><td>Capacitance Change</td><td>Within ± 30% of initial value</td></tr><tr><td>Tanδ</td><td>Less than 300% of specified value</td></tr><tr><td>Leakage Current</td><td>Within specified value</td></tr></table> * The above specifications shall be satisfied when the capacitors are restored to 20℃ after the rated voltage applied for 2,000 hours at 105℃.	Test Time	2,000 Hrs	Capacitance Change	Within ± 30% of initial value	Tanδ	Less than 300% of specified value	Leakage Current	Within specified value															
Test Time	2,000 Hrs																							
Capacitance Change	Within ± 30% of initial value																							
Tanδ	Less than 300% of specified value																							
Leakage Current	Within specified value																							
Shelf Life Test	Test time: 1,000 hours; other items are the same as those for the Endurance.																							
Ripple Current and Frequency Multipliers	<table><tr><td>Frequency (Hz)</td><td>50, 60</td><td>120</td><td>1k</td><td>10k up</td></tr><tr><td>Multiplier</td><td>0.60</td><td>0.70</td><td>0.85</td><td>1.0</td></tr></table>	Frequency (Hz)	50, 60	120	1k	10k up	Multiplier	0.60	0.70	0.85	1.0													
Frequency (Hz)	50, 60	120	1k	10k up																				
Multiplier	0.60	0.70	0.85	1.0																				

Diagram of Dimensions



Lead Spacing and Diameter


Unit: mm

φD	L	A	B	C	W	P
5	5.8 ± 0.3	5.3	5.3	5.9	0.5 ~ 0.8	1.5
6.3	5.8 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0
6.3	7.7 ± 0.3	6.6	6.6	7.2	0.5 ~ 0.8	2.0
8	6.5 ± 0.3	8.3	8.3	9.0	0.5 ~ 0.8	2.3
8	10 ± 0.5	8.3	8.3	9.0	0.7 ~ 1.1	3.1
10	10 ± 0.5	10.3	10.3	11	0.7 ~ 1.1	4.7
10	12.5 ± 0.5	10.3	10.3	11	0.7 ~ 1.1	4.7


The diagram is marking " () " for reference dimension.

Marking

φD ≤ 6.3 mm



φD = 8 ~ 10 mm





Dimension: $\phi D \times L$ (mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Impedance: Ω / at 100k Hz, 20°C

Dimension and Permissible Ripple Current

Rated Volt. (V _{DC})		6.3V (0J)			10V (1A)			16V (1C)			25V (1E)			35V (1V)			50V (1H)		
Cap. (μF)	Contents	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA	$\phi D \times L$	Imp.	mA
22	220							5×5.8	0.36	240	5×5.8	0.36	240	5×5.8	0.36	240			
33	330				5×5.8	0.36	240				5×5.8	0.36	240	6.3×5.8	0.26	300			
47	470	5×5.8	0.36	240				5×5.8	0.36	240	6.3×5.8	0.26	300	6.3×5.8	0.26	300			
68	680							6.3×5.8	0.26	300	6.3×5.8	0.26	300	6.3×7.7	0.16	600			
100	101	5×5.8	0.36	240	5×5.8	0.36	240	6.3×5.8	0.26	300	6.3×5.8	0.26	300	8×10	0.08	850	8×10	0.18	670
		6.3×5.8	0.26	300				6.3×7.7	0.16	600	6.3×7.7	0.16	600	8×6.5	0.18	500			
150	151				6.3×5.8	0.26	300	6.3×7.7	0.16	600	8×10	0.08	850	8×10	0.08	850			
220	221	6.3×5.8	0.26	300	6.3×7.7	0.16	600	6.3×7.7	0.16	600	8×10	0.08	850				10×10	0.15	900
					8×6.5	0.18	500	8×6.5	0.18	500									
330	331	6.3×7.7	0.16	600	8×10	0.08	850	8×10	0.08	850				10×10	0.06	1,190			
		8×6.5	0.18	500															
470	471	8×10	0.08	850	8×10	0.08	850	8×10	0.08	850	10×10	0.06	1,190	10×12.5	0.06	1,190			
680	681	8×10	0.08	850	8×10	0.08	850	10×10	0.06	1,190	10×12.5	0.06	1,190						
1,000	102				10×10	0.06	1,190	10×12.5	0.06	1,190									
1,500	152	10×10	0.06	1,190	10×12.5	0.06	1,190												
2,200	222	10×12.5	0.06	1,190															

Part Numbering System

VZS Series	470μF	± 20%	6.3V	Carrier Tape	8 ϕ × 10L	General Purpose
VZS	471	M	0J	TR	-	0810
Series Name	Capacitance	Capacitance Tolerance	Rated Voltage	Package Type	Terminal Type	Case Size
						Application

Note: For more details, please refer to "Part Numbering System - SMD Type" on page 106.