






DATE	REV	ECN	APP'D. BY
10-6-15	A2	10435	TRM
2-19-16	A3	10557	TRM




ISOMETRIC VIEW OF TERMINATED PLUG




- NOTES:
- 1. PLUG KIT CONSISTS OF:
PRE-INSERTED PLUG BODY - 39100-310
LOAD BAR - 39100-883
WIRE ALIGNER - 39100-864
GROMMET - 39100-886
 - 2. MATERIALS:
PLUG BODY: CLEAR POLYCARBONATE, UL 94-V0
LOAD BAR: RED POLYCARBONATE, UL 94-V0
WIRE ALIGNER: CLEAR POLYCARBONATE, UL 94-V0
GROMMET: CLEAR POLYCARBONATE, UL 94-V0
CONTACTS: COPPER ALLOY, SELECTIVE GOLD PLATING
 - 3. FOR PRODUCT SPECIFICATION SEE PR026-01.
 - 4. CONTACTS TERMINATE SOLID OR STRANDED CONDUCTORS BETWEEN .025 [0.64] TO .030 [0.76] OUTSIDE DIAMETER OF INSULATION.
 - 5. PRODUCT DESIGNED FOR CATEGORY 6 APPLICATIONS.
 - 6. DIMENSIONS AND TOLERANCES COMPLY WITH TIA-1096 STANDARD FORMERLY FCC/CFR 47, PART 68.
- △ TERMINATED PLUG HEIGHT: .237 [6.02] ±.005 [0.13].




PRE-INSERTED PLUG BODY 39100-310



GROMMET 39100-886



WIRE ALIGNER 39100-864



LOAD BAR 39100-883



50 MICRO-INCHES [1.27um]	SS-39100-039
CONTACT PLATING IN MATING AREA	PART NUMBER

THIRD ANGLE PROJECTION

11118 Susquehanna Trail South
Glen Rock, PA 17327-9199
(717) 235-7512
<http://www.stewartconnector.com>

DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: 8 CONDUCTOR, 8 POSITION UNSHIELDED CAT 6 PLUG, WITH LOAD BAR, WIRE ALIGNER AND GROMMET, .160 MAX CABLE, SCS

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ± 1°

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: [HTTP://BELFUSE.COM/STEWART/STEWART_PATENTS/](http://BELFUSE.COM/STEWART/STEWART_PATENTS/)

DRN BY: SAW DATE 3-17-14

APPD BY: DHG DATE 6-3-14

DWG NO. CT390119 REV. A3

SHEET NO. 1 OF 1